


TCP Item Number: 31032841 Lamp code: F32T8/841



Average Rated Life (hours)
 3 hours per start ----- 24,000

TCLP Compliant ----- Yes
 Low Mercury ----- Yes

Physical Characteristics

Lamp type ----- T8
 Base type ----- BiPin (G13)
 Lamp Material ----- Soda Lime
 Phosphor ----- Tri-Phosphor

Lamp Diameter (inches)
 Nominal (D) ----- 1.00
 Maximum (D) ----- 1.10
 Minimum (D) ----- .94

Overall Length (inches)
 Nominal (C) ----- 48.00
 Maximum (C) ----- 47.78
 Minimum (C) ----- 47.67

Face to End of opposing pin (inches)
 Maximum (B) ----- 47.50
 Minimum (B) ----- 47.40

Photometric Characteristics

Initial Lumens ----- 2950
 Mean Lumens (40% of rated life) ----- 2800
 Correlated Color Temperature (Kelvin) ----- 4100
 Color Rendering Index (CRI) ----- 85
 Normal Efficacy (Lumens/Watts) ----- 92

Electrical Characteristics


Lamp Watts ----- 32
 Nominal Lamp Volts ----- 132
 Nominal Lamp Operating Frequency (Hz) -- 50-60 Hz
 Min. Starting Lamp Voltage at 10°C ----- 300
 Min. Cathode Resistance (Rh/Rc) ----- 4.25
 Max. Cathode Resistance (Rh/Rc) ----- 6.50

24 MONTH
 STANDARD WARRANTY


For the most up-to-date specs, please visit www.tcpi.com

*Testing performed with Instant Start Ballast.


Spectral Power Distribution




Lamp Lumen Maintenance



Typical Lamp Mortality



TCP Item Number: 31032841 Lamp code: F32T8/841



Average Rated Life (hours)
 3 hours per start ----- 24,000

TCLP Compliant ----- Yes

Low Mercury ----- Yes

Physical Characteristics

Lamp type ----- T8

Base type ----- BiPin (G13)

Lamp Material ----- Soda Lime

Phosphor ----- Tri-Phosphor

Lamp Diameter (inches)

Nominal (D) ----- 1.00

Maximum (D) ----- 1.10

Minimum (D) ----- .94

Overall Length (inches)

Nominal (C) ----- 48.00

Maximum (C) ----- 47.78

Minimum (C) ----- 47.67

Face to End of opposing pin (inches)

Maximum (B) ----- 47.50

Minimum (B) ----- 47.40

Photometric Characteristics

Initial Lumens ----- 2950

Mean Lumens (40% of rated life) ----- 2800

Correlated Color Temperature (Kelvin) ----- 4100

Color Rendering Index (CRI) ----- 85

Normal Efficacy (Lumens/Watts) ----- 92

Electrical Characteristics

Lamp Watts ----- 32

Nominal Lamp Volts ----- 132

Nominal Lamp Operating Frequency (Hz) -- 50-60 Hz

Min. Starting Lamp Voltage at 10°C ----- 300

Min. Cathode Resistance (Rh/Rc) ----- 4.25


Max. Cathode Resistance (Rh/Rc) ----- 6.50

24 MONTH
 STANDARD WARRANTY


For the most up-to-date specs, please visit www.tcpi.com

*Testing performed with Instant Start Ballast.

Spectral Power Distribution



Lamp Lumen Maintenance



Typical Lamp Mortality

