



## SAFETY DATA SHEET

# RECTORSEAL® TRU-BLU™

Vibration resistant pipe thread sealant

### SECTION 1 – PRODUCT AND COMPANY INFORMATION

**Product Name**

Rectorseal® Tru-Blue™

**Product Codes**

31300, 31431, 31551, 31552, 31631, 31780, 31782, 31785

**Chemical Family**

Organic

**Use**

Pipe thread sealant

**Manufacturer's Name**

The RectorSeal Corporation  
2601 Spenwick Drive  
Houston, Texas 77055 USA

**Date of Validation**

June 14, 2016

**Date of Preparation**

June 14, 2016

**HMIS Codes**

Health	1
Flammability	2
Reactivity	0
PPI	B

**Emergency Telephone No.**

Chemtrec 24 Hours  
(800)-424-9300 USA  
(703)-527-3887 International

**Technical Service Telephone No.**

(800)-231-3345 or (713)-263-8001

### SECTION 2 – HAZARDS IDENTIFICATION

#### EMERGENCY OVERVIEW

**OSHA Hazards**

Combustable

**Target Organs**

Not Classified

#### GHS CLASSIFICATION

**Physical Hazards**

Combustable liquid (Category 4)

**Health Hazards**

**Acute Toxicity:**

Oral: Not Classified

Dermal: Not Classified

Inhalation: Not Classified

Skin Corrosion/Irritation: Not Classified  
Serious Eye Damage/Eye Irritation: Not Classified  
Skin Sensitization: Not Classified  
Respiratory Sensitization: Not Classified  
Germ Cell Mutagenicity: Not Classified  
Carcinogenicity: See Section 11  
Reproductive Toxicology: Not Classified  
Target Organ Systemic Toxicity - Single Exposure: Not Classified  
Target Organ Systemic Toxicity - Repeated Exposure: Not Classified

Aspiration Toxicity: Not Classified

## GHS Label elements, including precautionary statements



GHS07: Exclamation Mark

Signal Word: **Warning**

### Hazard Statements

H303 - May be harmful if swallowed.

H313 - May be harmful in contact with skin.

H335 + H336 - May cause respiratory irritation, and drowsiness or dizziness.

### Precautionary Statements

P102 - Keep out of reach of children.

P210 - Keep away from heat/sparks/open flames/hot surfaces. - No smoking

P240 - Ground/Bond container and receiving equipment

P261 - Avoid breathing dust/fume/gas/mist/vapors/spray

P262 - Do not get in eyes, on skin, or on clothing.

P264 - Wash hands thoroughly after handling.

P280 - Wear protective gloves/protective clothing/eye protection/face protection.

P301 + P310 - IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician.

P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P362 - Take off contaminated clothing and wash before reuse.

EUH066 - Repeated exposure may cause skin dryness or cracking

Precautionary Statements - EU No. 1272/2008

## Summary Of Acute Hazards

Irritation to eyes, nose and throat; drowsiness, narcosis, tremors and other CNS effects at high concentration.

## Route Of Exposure, Signs And Symptoms

### INHALATION

Nasal and respiratory irritation, dizziness, narcosis, headache, nausea, CNS depression and unconsciousness.

### EYE CONTACT

Watering, blurred vision, inflammation and irritation which can result in corneal injury.

### SKIN CONTACT

Irritation, dermatitis.

## INGESTION

Nausea, vomiting; CNS depression; irritation of gastrointestinal tract, liver and peritoneal wall; lung congestion.

## SUMMARY OF CHRONIC HAZARDS

Skin irritation and dermatitis. Possible liver and kidney damage.

## MEDICAL CONDITIONS AGGRAVATED BY EXPOSURE

Individuals with pre-existing or chronic diseases of the eyes, skin, respiratory system, cardiovascular system, gastrointestinal system, liver or kidneys may have increased susceptibility to excessive exposures.

## SECTION 3 – COMPOSITION/INFORMATION ON INGREDIENTS

Ingredient:	Diacetone Alcohol
Percentage By Weight:	20-30
CAS Number:	123-42-2
EC#:	204-626-7

## SECTION 4 – FIRST AID MEASURES

If inhaled:	If overcome by exposure, remove victim to fresh air immediately. Give oxygen or artificial respiration as needed. Obtain emergency medical attention. Prompt action is essential.
If on skin:	Wash with soap and water. If irritation occurs, seek medical attention
If in eyes:	Flush eyes with large amounts of water for 15 minutes. Get medical attention.
If swallowed:	If swallowed, call a physician immediately. Only induce vomiting at the instruction of a physician. Never give anything by mouth to an unconscious person.

## SECTION 5 – FIRE FIGHTING MEASURES

Flash point:	150°F (65°C)
LEL:	N/D
UEL:	N/D

### Extinguishing Media

Foam, dry chemical, carbon dioxide or water fog.

**Special Fire Fighting Procedures:** Wear self-contained breathing apparatus (SCBA) and other protective clothing. Hazardous decomposition products possible (see Section 10).

**Unusual Fire And Explosion Hazards:** Combustible – moderate flash point. Vapors heavier than air and may travel along the ground or to low spots at considerable distances to a source of ignition resulting in potential flashback. Burning liquid may float on water. Heat may build up pressure and rupture containers.

## SECTION 6 – ACCIDENTAL RELEASE MEASURES

**Steps To Be Taken In Case Material Is Released Or Spilled:** Remove all sources of ignition. Use absorbent materials to prevent footing hazard and to contain. Ventilate area with natural or explosion-proof, forced air ventilation. Avoid flushing into sewers, drains, waterways, and soil. Wear protective clothing and respiratory protection during cleanup.

## SECTION 7 – HANDLING AND STORAGE

**Precautions To Be Taken In Handling And Storing:** Keep container closed and upright when not in use. Do not store near heat, sparks, or open flames.

**Other Precautions:** Avoid prolonged or repeated contact with skin or clothing. Empty containers may contain residues; treat as if full and observe all products precautions. Do not reuse empty containers.

KEEP OUT OF REACH OF CHILDREN.

## SECTION 8 – EXPOSURE CONTROLS/PERSONAL PROTECTION

Ingredient	Units
------------	-------

**Diacetone Alcohol**

ACGIH TLV:	50 ppm
------------	--------

OSHA PEL:	50 ppm
-----------	--------

**Respiratory Protection (Specify Type):** In confined poorly ventilated areas, use NIOSH/MSHA approved air purifying or supplied air purifying or supplied air respirators.

**Ventilation – Local Exhaust:** Acceptable

**Special:** Explosion-proof equipment.

**Mechanical (General):** Preferable

**Other:** N/A

**Protective Gloves:** Wear rubber gloves.

**Eye Protection:** Chemical splash goggles (ANSI Z-87.1 or equivalent)

**Other Protective Clothing Or Equipment:** Coveralls recommended.

**Work/Hygienic Practices:** Where use can result in skin contact, wash exposed areas thoroughly before eating, drinking, smoking, or leaving work area. Launder contaminated clothing before reuse.

## SECTION 9 – PHYSICAL AND CHEMICAL PROPERTIES

Boiling point:	322°F (161°C) @ 760 mmHg
Specific gravity (H2O = 1):	1.38
Vapor pressure (mmHg):	0.3 @ 68°F (20°C)
Melting point:	N/A
Vapor Density (Air = 1):	1.1
Evaporation rate (Ethyl Acetate = 1):	0.14
Appearance/Odor:	Blue paste/Mild odor
Solubility in water:	23%
Volatile Organic Compounds (VOC) Content (theoretical percentage by weight):	23% or (317 g/L)

## SECTION 10 – STABILITY AND REACTIVITY

**Stability:** Stable

**Conditions To Avoid:** Heat, sparks, open flames, and strong oxidizing. Temperatures above 500°F (260°C).

**Incompatibility (Materials To Avoid):** Gaseous oxygen, strong oxidizing materials, molten alkali metals.

**Hazardous Decomposition Products:** CO, CO<sub>2</sub> and fragmented hydrocarbons.

**Hazardous Polymerization:** Will not occur.

## SECTION 11 – TOXICOLOGY INFORMATION

### Chronic Health Hazards

No ingredient in this product is an IARC, NTP or OSHA Lister carcinogen.

### Toxicology Data

#### Ingredient Name

Diacetone Alcohol	
Oral-Rat LD50:	4000 mg/kg
Inhalation-Human TCLo:	100 ppm

## SECTION 12 – ECOLOGICAL INFORMATION

### Ecological Data

Ingredient Name:	Diacetone Alcohol
Food Chain Concentration Potential	N/A
Waterfowl Toxicity	N/A
BOD	N/A
Aquatic Toxicity	N/A

## SECTION 13 – DISPOSAL CONSIDERATIONS

**Waste Classification:** Non-regulated solid waste

**Disposal Method:** Approved landfill

Waste from this product is not considered hazardous as defined under the Resource Conservation and Recovery Act (RCRA) 40 CFR 261. Dispose of in accordance with Federal, State, and Local regulation regarding pollution.

## SECTION 14 – TRANSPORTATION INFORMATION

DOT:	Non-regulated
Ocean (IMDG):	Non-regulated
Air (IATA):	Non-regulated
WHMIS (Canada):	Non-regulated

## SECTION 15 – REGULATORY INFORMATION

### Regulatory Data

Ingredient Name:	Diacetone Alcohol
SARA 313	N/A
TSCA Inventory	Yes
CERCLA RQ	N/A
RCRA Code	N/A

## SECTION 16 – OTHER INFORMATION

This document is prepared pursuant to the OSHA Hazard Communication Standard (29 CFR 1910.1200). The information herein is given in good faith, but no warranty, expressed or implied is made.

Consult RectorSeal for further information: (713) 263-8001



SAFETY DATA SHEET

RECTORSEAL® TRU-BLU™  
Vibration resistant pipe thread sealant

SECTION 1 – PRODUCT AND COMPANY INFORMATION

Product Name  
Rectorseal® Tru-Blue™  
Product Codes  
31300, 31431, 31551, 31552, 31631, 31780, 31782, 31785  
Chemical Family  
Organic  
Use  
Pipe thread sealant  
Manufacturer's Name  
The RectorSeal Corporation  
2601 Spenwick Drive  
Houston, Texas 77055 USA  
Date of Validation  
June 14, 2016  
Date of Preparation  
June 14, 2016

HMIS Codes  
Health 1  
Flammability 2  
Reactivity 0  
PPI B

Emergency Telephone No.  
Chemtrec 24 Hours  
(800)-424-9300 USA  
(703)-527-3887 International

Technical Service Telephone No.  
(800)-231-3345 or (713)-263-8001

SECTION 2 – HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

OSHA Hazards  
Combustable

Target Organs  
Not Classified

GHS CLASSIFICATION

Physical Hazards  
Combustable liquid (Category 4)

Health Hazards

Acute Toxicity:  
Oral: Not Classified  
Dermal: Not Classified  
Inhalation: Not Classified

Skin Corrosion/Irritation: Not Classified  
Serious Eye Damage/Eye Irritation: Not Classified  
Skin Sensitization: Not Classified  
Respiratory Sensitization: Not Classified  
Germ Cell Mutagenicity: Not Classified  
Carcinogenicity: See Section 11  
Reproductive Toxicology: Not Classified  
Target Organ Systemic Toxicity - Single Exposure: Not Classified  
Target Organ Systemic Toxicity - Repeated Exposure: Not Classified

Aspiration Toxicity: Not Classified

## GHS Label elements, including precautionary statements



GHS07: Exclamation Mark

Signal Word: **Warning**

### Hazard Statements

H303 - May be harmful if swallowed.

H313 - May be harmful in contact with skin.

H335 + H336 - May cause respiratory irritation, and drowsiness or dizziness.

### Precautionary Statements

P102 - Keep out of reach of children.

P210 - Keep away from heat/sparks/open flames/hot surfaces. - No smoking

P240 - Ground/Bond container and receiving equipment

P261 - Avoid breathing dust/fume/gas/mist/vapors/spray

P262 - Do not get in eyes, on skin, or on clothing.

P264 - Wash hands thoroughly after handling.

P280 - Wear protective gloves/protective clothing/eye protection/face protection.

P301 + P310 - IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician.

P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P362 - Take off contaminated clothing and wash before reuse.

EUH066 - Repeated exposure may cause skin dryness or cracking

Precautionary Statements - EU No. 1272/2008

## Summary Of Acute Hazards

Irritation to eyes, nose and throat; drowsiness, narcosis, tremors and other CNS effects at high concentration.

## Route Of Exposure, Signs And Symptoms

### INHALATION

Nasal and respiratory irritation, dizziness, narcosis, headache, nausea, CNS depression and unconsciousness.

### EYE CONTACT

Watering, blurred vision, inflammation and irritation which can result in corneal injury.

### SKIN CONTACT



Irritation, dermatitis.

## INGESTION

Nausea, vomiting; CNS depression; irritation of gastrointestinal tract, liver and peritoneal wall; lung congestion.

## SUMMARY OF CHRONIC HAZARDS

Skin irritation and dermatitis. Possible liver and kidney damage.

## MEDICAL CONDITIONS AGGRAVATED BY EXPOSURE

Individuals with pre-existing or chronic diseases of the eyes, skin, respiratory system, cardiovascular system, gastrointestinal system, liver or kidneys may have increased susceptibility to excessive exposures.

## SECTION 3 – COMPOSITION/INFORMATION ON INGREDIENTS

Ingredient:	Diacetone Alcohol
Percentage By Weight:	20-30
CAS Number:	123-42-2
EC#:	204-626-7

## SECTION 4 – FIRST AID MEASURES

If inhaled:	If overcome by exposure, remove victim to fresh air immediately. Give oxygen or artificial respiration as needed. Obtain emergency medical attention. Prompt action is essential.
If on skin:	Wash with soap and water. If irritation occurs, seek medical attention
If in eyes:	Flush eyes with large amounts of water for 15 minutes. Get medical attention.
If swallowed:	If swallowed, call a physician immediately. Only induce vomiting at the instruction of a physician. Never give anything by mouth to an unconscious person.

## SECTION 5 – FIRE FIGHTING MEASURES

Flash point:	150°F (65°C)
LEL:	N/D
UEL:	N/D

### Extinguishing Media

Foam, dry chemical, carbon dioxide or water fog.

**Special Fire Fighting Procedures:** Wear self-contained breathing apparatus (SCBA) and other protective clothing. Hazardous decomposition products possible (see Section 10).

**Unusual Fire And Explosion Hazards:** Combustible – moderate flash point. Vapors heavier than air and may travel along the ground or to low spots at considerable distances to a source of ignition resulting in potential flashback. Burning liquid may float on water. Heat may build up pressure and rupture containers.

## SECTION 6 – ACCIDENTAL RELEASE MEASURES

**Steps To Be Taken In Case Material Is Released Or Spilled:** Remove all sources of ignition. Use absorbent materials to prevent footing hazard and to contain. Ventilate area with natural or explosion-proof, forced air ventilation. Avoid flushing into sewers, drains, waterways, and soil. Wear protective clothing and respiratory protection during cleanup.

## SECTION 7 – HANDLING AND STORAGE

**Precautions To Be Taken In Handling And Storing:** Keep container closed and upright when not in use. Do not store near heat, sparks, or open flames.

**Other Precautions:** Avoid prolonged or repeated contact with skin or clothing. Empty containers may contain residues; treat as if full and observe all products precautions. Do not reuse empty containers.

KEEP OUT OF REACH OF CHILDREN.

## SECTION 8 – EXPOSURE CONTROLS/PERSONAL PROTECTION

Ingredient	Units
------------	-------

**Diacetone Alcohol**

ACGIH TLV:	50 ppm
------------	--------

OSHA PEL:	50 ppm
-----------	--------

**Respiratory Protection (Specify Type):** In confined poorly ventilated areas, use NIOSH/MSHA approved air purifying or supplied air purifying or supplied air respirators.

**Ventilation – Local Exhaust:** Acceptable

**Special:** Explosion-proof equipment.

**Mechanical (General):** Preferable

**Other:** N/A

**Protective Gloves:** Wear rubber gloves.

**Eye Protection:** Chemical splash goggles (ANSI Z-87.1 or equivalent)

**Other Protective Clothing Or Equipment:** Coveralls recommended.

**Work/Hygienic Practices:** Where use can result in skin contact, wash exposed areas thoroughly before eating, drinking, smoking, or leaving work area. Launder contaminated clothing before reuse.

## SECTION 9 – PHYSICAL AND CHEMICAL PROPERTIES

Boiling point:	322°F (161°C) @ 760 mmHg
Specific gravity (H2O = 1):	1.38
Vapor pressure (mmHg):	0.3 @ 68°F (20°C)
Melting point:	N/A
Vapor Density (Air = 1):	1.1
Evaporation rate (Ethyl Acetate = 1):	0.14
Appearance/Odor:	Blue paste/Mild odor
Solubility in water:	23%
Volatile Organic Compounds (VOC) Content (theoretical percentage by weight):	23% or (317 g/L)

## SECTION 10 – STABILITY AND REACTIVITY

**Stability:** Stable

**Conditions To Avoid:** Heat, sparks, open flames, and strong oxidizing. Temperatures above 500°F (260°C).

**Incompatibility (Materials To Avoid):** Gaseous oxygen, strong oxidizing materials, molten alkali metals.

**Hazardous Decomposition Products:** CO, CO<sub>2</sub> and fragmented hydrocarbons.

**Hazardous Polymerization:** Will not occur.

## SECTION 11 – TOXICOLOGY INFORMATION

### Chronic Health Hazards

No ingredient in this product is an IARC, NTP or OSHA Lister carcinogen.

### Toxicology Data

#### Ingredient Name

Diacetone Alcohol	
Oral-Rat LD50:	4000 mg/kg
Inhalation-Human TCLo:	100 ppm

## SECTION 12 – ECOLOGICAL INFORMATION

### Ecological Data

Ingredient Name:	Diacetone Alcohol
Food Chain Concentration Potential	N/A
Waterfowl Toxicity	N/A
BOD	N/A
Aquatic Toxicity	N/A

## SECTION 13 – DISPOSAL CONSIDERATIONS

**Waste Classification:** Non-regulated solid waste

**Disposal Method:** Approved landfill

Waste from this product is not considered hazardous as defined under the Resource Conservation and Recovery Act (RCRA) 40 CFR 261. Dispose of in accordance with Federal, State, and Local regulation regarding pollution.

## SECTION 14 – TRANSPORTATION INFORMATION

DOT:	Non-regulated
Ocean (IMDG):	Non-regulated
Air (IATA):	Non-regulated
WHMIS (Canada):	Non-regulated

## SECTION 15 – REGULATORY INFORMATION

### Regulatory Data

Ingredient Name:	Diacetone Alcohol
SARA 313	N/A
TSCA Inventory	Yes
CERCLA RQ	N/A
RCRA Code	N/A

## SECTION 16 – OTHER INFORMATION

This document is prepared pursuant to the OSHA Hazard Communication Standard (29 CFR 1910.1200). The information herein is given in good faith, but no warranty, expressed or implied is made.

Consult RectorSeal for further information: (713) 263-8001