



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



46605 Thermo-Shrink Thin HT SHRINK Disk, 4' L, 1/4" Id

Ideal

| | |
|------------------|--|
| Catalog Number | 46605 |
| Manufacturer | Ideal |
| Description | Ideal, Heat Shrinkable Tube, Thermo-Shrink, Thin-Wall, Shrink Ratio: 2:1, Inside Diameter: 1/4 In, Thickness: 022 In, Length: 4 FT, Volume Resistivity: 1014 Ohm CM For Astm D 876 Test Method, Dielectric Strength: Astm D 150, 20 KV/MM, Continuous Operating Temperature: -55 to 125 Deg C, Minimum Shrink Temperature: 70 Deg C, Heat Shock: UI 224, No Cracking (250 Deg C/4 HR), Cable Range: 14 - 8 Awg, Nominal Recovered I.D. (Max.): 0.126 In, Expanded I.D. (Min.): 0.268, Elongation At Break: 600 PCT Astm D 638, E |
| Weight per unit | 0.1200 (lbs/each) |
| Product Category | Insulating Materials |

Features

| | |
|-------------------------------|----------------------|
| continuous operating temperat | -55 To 125 |
| Dielectric Strength | ASTM D 150, 20 KV/MM |
| Inside Diameter | 1/4 |
| Shrink Ratio | 2:1 |

Dimensions and Weight

| | |
|-----------|-----|
| Length | 4 |
| Thickness | 022 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | THERMO-SHRINK THIN HT SHRNK DISK, 4' L, 1/4" ID |
| extra long description | IDEAL 46-605 HEAT SHRINKABLE TUBING |
| Features | Polyolefin material electrically insulates and protects in-line components, disconnect terminals and splices with its high strength and excellent resilienceUse to bundle wires for very flexible light-duty harnessesHighly flame-retardant and flexible; resistant to common fluids and solventsMeets UL 486D 125°C VW-1 600V; Material: No PBB's, PBBE's, conforms to ROHS2:1 shrink ratio; Minimum shrink temperature: 70°C; Operating temperature: -55°C to +125°CRoHS compliantUV resistant |
| Long Description | IDEAL, Heat Shrinkable Tube, Thermo-Shrink, Thin-Wall, Shrink Ratio: 2:1, Inside Diameter: 1/4 IN, Thickness: 022 IN, Length: 4 FT, Volume Resistivity: 1014 OHM CM For ASTM D 876 Test Method, Dielectric Strength: ASTM D 150, 20 KV/MM, Continuous Operating Temperature: -55 To 125 DEG C, Minimum Shrink Temperature: 70 DEG C, Heat Shock: UL 224, No Cracking (250 DEG C/4 HR), Cable Range: 14 - 8 AWG, Nominal Recoveredi.d. (max.): 0.126 IN, Expanded I.d. (min.): 0.268, Elongation At Break: 600 PCT ASTM D 638, E |
| Product Type | Heat Shrinkable Tubing |
| Special Features | Features: Polyolefin material electrically insulates and protects in-line components, disconnect terminals and splices with its high strength and excellent resilience; Use to bundle wires for very flexible light-duty harnesses; Highly flame-retardant and flexible; Resistant to common fluids and solvents; Meets UL 486D 125°C VW-1 600V; Material: No PBBs, PBBEs, conforms to ROHS;; Cable Range: 14 - 8 AWG; Nominal Recoveredi.d. (max.): 0.126 IN; Expanded I.d. (min.): 0.268; Elongation At Break: 600 PCT ASTM D |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250466054 |
| Manufacturers Part Number | 46-605 |
| UPC | 783250466054 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------|
| Category Description | HEAT/COLD SHRINK |
| Type | Thin-Wall |

Packaging

| | |
|-----------------|------|
| Carton | 5 |
| Weight Per each | 0.12 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

C/US RU Listed, RoHS
