



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## 380G 1" STL FM8 CVR W/Gasket *Crouse-Hinds*

Catalog Number	380G
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Form 8 Cover With Integral Gasket, Sheet Steel, 1"
Weight per unit	0.2040 (lbs/each)
Product Category	Bodies & Covers

### Features

dimensions	1.7500 IN X 0.2500 IN X 5.5900 IN
Material	Sheet Steel

### Descriptions

Description	1" STL FM8 CVR W/GASKET
extra long description	CRS-H 380G 1 SHT STEEL FORM 8 CVR/G
Features	One hundred years after the introduction of the Condulet, Eaton remains the leader in conduit outlet bodies with its Crouse-Hinds series. The line has grown to six families manufactured in a variety of materials, and Form 8 bodies are offered in seven different shapes to provide the most flexible offering on the market. Form 8 Condulet outlet bodies provide more room for heavier conductors. Many shapes and sizes are available for rigid threaded conduit. Two cover screws on all body sizes provide tight
Long Description	Eaton Crouse-Hinds series Condulet Form 8 cover with integral gasket, Sheet steel, 1"
Product Type	1 SHT Steel Form 8 CVR/Gask
Special Features	With Neoprene Integral Gasket

### Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00662276018327
Manufacturers Part Number	380G
UPC	662276018327

### Taxonomies, Classifications, and Categories

Category Description	FORM 7, 8, CONDULETS, COVERS, & GASKETS
Type	Cover with integral gasket

### Packaging

Carton	1
Package	25
Weight Per each	0.204



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	UL 514B, CSA C22.2, FEDERAL SPECIFICATION W-C-586D