ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2255 Northwest Parkway SE
Marietta, GA 30067-0000
Phone: 6783984904
Fax: 6783984905



406 DETECTABLE BURIED BARRICADE TAPE, 3" X 1000', RD

MINNESOTA MINING (3M)

Catalog Number	406
Manufacturer	MINNESOTA MINING (3M)
Description	Barricade Tape, Red, Black Legend Color, Aluminum Foil Backing Material, Non-Adhesive, Silicone Adhesive Material, 35 lb/in;15000 psi Tensile Strength, Caution Buried Electric Line Below Legend, English,+200 °F Operating Temperature, 1000 ft Length, 3 in Width, 0.005 in Thickness, 5 yr Shelf Life, 5.7 lb/EA
Weight per unit	5.7 (lbs/each)
Product Category	Markers & Marking Tapes

Descriptions

Description	DETECTABLE BURIED BARRICADE TAPE, 3" X 1000', RD
Features	Ensure precision location of underground assets by using Scotch® 406 Buried Barricade Tape. Utilizing this aluminum foil-backed tape when burying wires or cables helps others avoid dangerous mistakes when digging and, by layering this tape above the line, it can easily be located with a non-ferrous metal detector. Do your part to keep fellow workers safe by having this tape handy for all your buried work. This tape has a layer of clear film laminate covering the message to protect it from harsh soil condit
Long Description	Scotch® Buried Barricade Tape 406 is a 5 mil thick, aluminum foil backing, buried barricade tape that is printed with a warning message. It is great for alerting pedestrians of danger in both small and large areas.
Product Type	Scotch® Detectable Buried Barricade Tape
Special Features	Caution Buried Electric Line Below
Extra Long Description	3M 7000133190 Scotch® Detectable Bu

Manufacturer Information

Brand	Scotch
	3M Electrical Products
GTIN	00051128577790
Manufacturers Part Number	406R3X1000FT
	7000133190
UPC	054007

Taxonomies, Classifications, and Categories

Category Description	TAPE
Type	Barricade Tape

2255 Northwest Parkway SE
Marietta, GA 30067-0000
Phone: 6783984904
Fax: 6783984905

Packaging

Carton	1
Package	8
Weight Per Each	5.7 (lbs/each)

Uses, Certifications, and Standards

Application	Buried

Scotch®

Detectable Buried Barricade Tapes 400 Series

Data Sheet **June 2010**

Description

Scotch® Detectable Buried Barricade Tapes 400 Series are nominal 5-mil tapes, constructed of a solid aluminum foil backing with a clear film laminate. The aluminum backing helps make underground assets easier to locate when using a non-ferrous locator. These tapes are color-coded to meet or exceed the industry standards, including the American Public Works Association (APWA).

Agency Approvals & Self Certifications

Meets the requirements of:

RoHS 2002/95/EC

"RoHS Compliant 2002/95/EC" means that the product or part ("Product") does not contain any of the substances in excess of the maximum concentration values in EU Directive 2002/95/EC, as amended by Commission Decision 2002/618/EC, unless the substance is in an application that is exempt under RoHS. This information represents 3M's knowledge and belief, which may be based in whole or in part on information provided by third party suppliers to 3M.

Typical Properties

Not for specifications. Values are typical, not to be considered minimum or maximum. Properties measured at room temperature 73°F (23°C) unless otherwise stated.

Physical Property (Test Method)	**Typical Value** US units (metric)
Color and Width	Variable (see availability chart)
Thickness	5-mil
Length	1000 ft.
Maximum Detectable Burial Range*	2" – 6" to 12" 3" – 12" to 24" 6" – 22" to 30"
Tensile Strength at Break (ASTM D-882)	35 lbs/in (15,000 psi)
* The types of locators used have a direct input on the maximum detectable burial depth.	

Specifications

The tape shall be of good manufacturing quality in terms of appearance. It shall not gap or telescope more than 0.1 inches when stored at temperatures below 49°C. It must be flexible or not be stiff or brittle in applications ranging from below 0°C to about 38°C. The tape must be removable from the roll without difficulty.

The tape shall be smooth, uniform, and free of defects and irregularities. The print shall be uniform, free of visibly large voids and foreign materials, and the lettering free of lumps. The warning words shall be legible, correctly spelled and fully printed. The ink shall be dry, firmly bonded to the substrate, and not transferable to non-printed parts of the film.

Shelf Life & Storage

This product has a 5-year shelf life from date of manufacture when stored in a humidity controlled storage (10°C/50°F to 27°C/80°F and <75% relative humidity).

3M

Scotch® Detectable Buried Barricade Tape 400 Series

Availability

Please contact your local distributor; available from 3M.com/electrical [Where to Buy] or call 1-800-245-3573.

Product	Text	Length	Color	Thickness	Width
Scotch 406	CAUTION BURIED ELECTRIC LINE BELOW	1000 ft.	Red	5-mil	3 in.
Scotch 408					6 in.
Scotch 407	CAUTION BURIED FIBER OPTIC LINE BELOW	1000 ft.	Orange	5-mil	3 in.
Scotch 409					6 in.
Scotch 410	CAUTION BURIED TELEPHONE LINE BELOW	1000 ft.	Orange	5-mil	3 in.
Scotch 411					6 in.
Scotch 412	CAUTION BURIED HIGH VOLTAGE CABLE BELOW	1000 ft.	Red	5-mil	3 in.
Scotch 413					6 in.
Scotch 414	CAUTION BURIED GAS LINE BELOW	1000 ft.	Yellow	5-mil	3 in.
Scotch 415					6 in.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product, which are not contained in 3M's current publications, or any contrary statements contained on your purchase order, shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability

This product will be free from defects in material and manufacture at the time of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.

3M is a trademark of 3M Company.
Scotch is a registered trademark of 3M Company.

3M

Electrical Markets Division
6801 River Place Boulevard
Austin, TX 78726-9000
800.245.3573 / 651.737.7222 (24 hours)
Fax: 800.245.0329
www.3m.com/electrical

Please recycle
© 3M 2010 All rights reserved
78-8127-8773-3 B