



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



5362B RCPT, Dup SB, Hubpro, 20A 125V, FG , BR Hubbell Wiring Devices

Catalog Number	5362B
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Brown
Weight per unit	0.0820 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Back and Side Wired
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	3-Wire
pallet quantity	3600
Phase	1
Poles	2-Pole
Voltage Rating	125 V
Wattage	1875
Wire Size	#12 to #10

Dimensions and Weight

Size	3.28 in x 1.41 in x 1.09 in;Standard Sized Product
------	--

Descriptions

Description	RCPT, DUP SB, HUBPRO, 20A 125V, FG , BR
extra long description	HWDK 5362B RCPT, DUP SB, HUBPRO, 20
Long Description	Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Brown
Product Type	RCPT, Dup SB, Hubpro, 20A 125V, FG , BR
Special Features	Self Grounding

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585834986
Manufacturers Part Number	5362B
series	Hubbell-PRO
UPC	783585834986



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Standard Duplex

Packaging

Carton	1
Package	10
Weight Per each	0.082

Uses, Certifications, and Standards

Application	Hubbell-Pro Extra Heavy Duty
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	5-20R
standard	UL File No. E2186, Certified to CSA 22.2, No. 42 File 285, Fed. Spec. W-C-596, NEMA® WD-6 Compliant