

# PASS & SEYMOUR®

## Specification Grade Single Receptacles 15 & 20A, 125, 250V


**5251, 5351, 5651, 5851**

### Long-term durability for commercial applications.

Tough nylon faces provide superior impact resistance. And the heavy-gauge steel straps provide added strength for tough applications. These dependable performers feature extra-durable, single-piece, triple-wipe brass power contacts, too.



### FEATURES & BENEFITS



### FIELD USES/VERTICAL MARKETS

- Retail
- Multiple Dwelling
- Hospitality/Lodging
- Office



# PASS & SEYMOUR®

## Specification Grade Single Receptacles 15 & 20A, 125, 250V

### ORDERING INFORMATION

| Catalog Number                                 | Rating |     | Color*       | NEMA Config. No. |
|--|--------|-----|--------------|------------------|
|  | A.     | V.  |              |                  |
| <b>Single Receptacles Back &amp; Side Wire</b> |        |     |              |                  |
| <b>5251I</b>                                   | 15     | 125 | Ivory        | 5-15R            |
| <b>5251W</b>                                   | 15     | 125 | White        | 5-15R            |
| <b>5251</b>                                    | 15     | 125 | Brown        | 5-15R            |
| <b>5251LA</b>                                  | 15     | 125 | Light Almond | 5-15R            |
| <b>5351I</b>                                   | 20     | 125 | Ivory        | 5-20R            |
| <b>5351W</b>                                   | 20     | 125 | White        | 5-20R            |
| <b>5351</b>                                    | 20     | 125 | Brown        | 5-20R            |
| <b>5351LA</b>                                  | 20     | 125 | Light Almond | 5-20R            |
| <b>5651I</b>                                   | 15     | 250 | Ivory        | 6-15R            |
| <b>5651W</b>                                   | 15     | 250 | White        | 6-15R            |
| <b>5651</b>                                    | 15     | 250 | Brown        | 6-15R            |
| <b>5651LA</b>                                  | 15     | 250 | Light Almond | 6-15R            |
| <b>5851I</b>                                   | 20     | 250 | Ivory        | 6-20R            |
| <b>5851W</b>                                   | 20     | 250 | White        | 6-20R            |
| <b>5851</b>                                    | 20     | 250 | Brown        | 6-20R            |
| <b>5851LA</b>                                  | 20     | 250 | Light Almond | 6-20R            |

\*Other colors available upon request. Please contact your local sales representative.



NEMA  
5-15R



NEMA  
5-20R



NEMA  
6-15R



NEMA  
6-20R

For more information on these and other P&S products refer to our Catalog or visit our web site.

# PASS & SEYMOUR®

## Specification Grade Single Receptacles 15 & 20A, 125, 250V



### TECHNICAL SPECIFICATIONS

#### 3rd Party Compliance

UL Listed, File Number E140596, Standard UL498; CSA Certified, Standard CSA-C22.2 No. 42.

#### Performance

##### Electrical


|                         |  |
|-------------------------|--|
| Dielectric Voltage      | Withstands 2000V minimum   |
| Maximum Working Voltage | 125V / 250V (5851 models)  |
| Current Interrupting    | Certified for current interrupting at full-rated current   |
| Temperature Rise        | Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current |

##### Mechanical

|                         |  |
|-------------------------|--|
| Terminal Identification | Terminal identification in accordance with UL498 (Brass, White, Green) |
| Terminal Accommodation  | #14 - #10 AWG copper conductor only                                    |
| Product Identification  | Ratings are a permanent part of the device                             |

##### Environmental

|              |         |
|--------------|---------|
| Flammability | UL94 V2 |
|--------------|---------|



**Dimensions for  
15 & 20 Amp**

#### Materials

|                |                 |                          |                 |
|----------------|-----------------|--------------------------|-----------------|
| Face           | Nylon           | Terminal Screws          | Tri-Drive Brass |
| Back Body      | PVC             | Hex Head Grounding Screw | Tri-Drive Zinc  |
| Contacts       | .032 (.8) Brass |                          | Plated Steel    |
| Clamping Plate | .080 Steel      | Assembly Rivets          | Steel           |
| Mounting Strap | .042 Steel      | Mounting Screws          | Tri-Drive Steel |

#### Warranty

1 Year

For more information on these and other P&S products refer to our Catalog or visit our web site.

#### ALSO AVAILABLE...

- Hospital Grade Devices
- SPD & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips



#### Electrical Wiring Systems

P.O. Box 4822  
Syracuse, NY 13221-4822  
Phone: 1.800.776.4035  
[www.legrand.us/passandseymour](http://www.legrand.us/passandseymour)

570 Applewood Crescent  
Vaughan, Ontario L4K 4B4  
Phone: 905.738.9195  
[www.legrand.ca](http://www.legrand.ca)


## 5251, 5351, 5651, 5851

### Long-term durability for commercial applications.

Tough nylon faces provide superior impact resistance. And the heavy-gauge steel straps provide added strength for tough applications. These dependable performers feature extra-durable, single-piece, triple-wipe brass power contacts, too.



#### FEATURES & BENEFITS



#### FIELD USES/VERTICAL MARKETS

- Retail
- Multiple Dwelling
- Hospitality/Lodging
- Office



# PASS & SEYMOUR®

## Specification Grade Single Receptacles 15 & 20A, 125, 250V

### ORDERING INFORMATION

| Catalog Number                                 | Rating |     | Color*       | NEMA Config. No. |
|--|--------|-----|--------------|------------------|
|  | A.     | V.  |              |                  |
| <b>Single Receptacles Back &amp; Side Wire</b> |        |     |              |                  |
| <b>5251I</b>                                   | 15     | 125 | Ivory        | 5-15R            |
| <b>5251W</b>                                   | 15     | 125 | White        | 5-15R            |
| <b>5251</b>                                    | 15     | 125 | Brown        | 5-15R            |
| <b>5251LA</b>                                  | 15     | 125 | Light Almond | 5-15R            |
| <b>5351I</b>                                   | 20     | 125 | Ivory        | 5-20R            |
| <b>5351W</b>                                   | 20     | 125 | White        | 5-20R            |
| <b>5351</b>                                    | 20     | 125 | Brown        | 5-20R            |
| <b>5351LA</b>                                  | 20     | 125 | Light Almond | 5-20R            |
| <b>5651I</b>                                   | 15     | 250 | Ivory        | 6-15R            |
| <b>5651W</b>                                   | 15     | 250 | White        | 6-15R            |
| <b>5651</b>                                    | 15     | 250 | Brown        | 6-15R            |
| <b>5651LA</b>                                  | 15     | 250 | Light Almond | 6-15R            |
| <b>5851I</b>                                   | 20     | 250 | Ivory        | 6-20R            |
| <b>5851W</b>                                   | 20     | 250 | White        | 6-20R            |
| <b>5851</b>                                    | 20     | 250 | Brown        | 6-20R            |
| <b>5851LA</b>                                  | 20     | 250 | Light Almond | 6-20R            |

\*Other colors available upon request. Please contact your local sales representative.



NEMA  
5-15R



NEMA  
5-20R



NEMA  
6-15R



NEMA  
6-20R

For more information on these and other P&S products refer to our Catalog or visit our web site.

# PASS & SEYMOUR®

## Specification Grade Single Receptacles 15 & 20A, 125, 250V



### TECHNICAL SPECIFICATIONS

#### 3rd Party Compliance

UL Listed, File Number E140596, Standard UL498; CSA Certified, Standard CSA-C22.2 No. 42.

#### Performance

##### Electrical


|                         |  |
|-------------------------|--|
| Dielectric Voltage      | Withstands 2000V minimum   |
| Maximum Working Voltage | 125V / 250V (5851 models)  |
| Current Interrupting    | Certified for current interrupting at full-rated current   |
| Temperature Rise        | Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current |

##### Mechanical

|                         |  |
|-------------------------|--|
| Terminal Identification | Terminal identification in accordance with UL498 (Brass, White, Green) |
| Terminal Accommodation  | #14 - #10 AWG copper conductor only                                    |
| Product Identification  | Ratings are a permanent part of the device                             |

##### Environmental

|              |         |
|--------------|---------|
| Flammability | UL94 V2 |
|--------------|---------|



**Dimensions for  
15 & 20 Amp**

#### Materials

|                |                 |                          |                             |
|----------------|-----------------|--------------------------|-----------------------------|
| Face           | Nylon           | Terminal Screws          | Tri-Drive Brass             |
| Back Body      | PVC             | Hex Head Grounding Screw | Tri-Drive Zinc Plated Steel |
| Contacts       | .032 (.8) Brass | Assembly Rivets          | Steel                       |
| Clamping Plate | .080 Steel      | Mounting Screws          | Tri-Drive Steel             |
| Mounting Strap | .042 Steel      |                          |                             |

#### Warranty

1 Year

For more information on these and other P&S products refer to our Catalog or visit our web site.

#### ALSO AVAILABLE...

- Hospital Grade Devices
- SPD & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips



#### Electrical Wiring Systems

P.O. Box 4822  
Syracuse, NY 13221-4822  
Phone: 1.800.776.4035  
[www.legrand.us/passandseymour](http://www.legrand.us/passandseymour)

570 Applewood Crescent  
Vaughan, Ontario L4K 4B4  
Phone: 905.738.9195  
[www.legrand.ca](http://www.legrand.ca)