



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 544621 1-3/4" SDS Max Demolition Hammer

*Milwaukee Electric Tool*

Catalog Number	544621
Manufacturer	Milwaukee Electric Tool
Description	Get Best-In-Class Power and The Highest Overload Protection For The Toughest Demolition Jobs. The SDS-Max Demolition Hammer Has A Heavy-Duty Crank Piston Mechanism That Delivers 8.8 FT-LBS Of Impact Energy For Hard-Hitting Performance In Any Concrete. For Lighter Applications, The Two-Speed Impact Mode Allows You to Reduce BPM to 2, 200. Advanced Constant Power Technology Electronics and A Mechanical Clutch Enhance Your Control and The Rotary Hammer'S Long-Term Durability. The Anti-Vibration System and Side
Weight per unit	25.3 (lbs/each)
Product Category	Power Tools - Corded

### Features

amperage rating	14
Chuck Capacity	1
Cord Length	8.0
Handle Type	D-Handle
Material	Metal
Voltage	120.0

### Dimensions and Weight

Height	12.0
Length	4.5
Width	18.0



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	1-3/4" SDS MAX DEMOLITION HAMMER
extra long description	MILW 5446-21 15 LB SDSMAX DEMO HAMM
Features	1-3/4 in. SDS Max Demolition Hammer
Long Description	Get best-in-class power and the highest overload protection for the toughest demolition jobs. The SDS-Max demolition hammer has a heavy-duty crank piston mechanism that delivers 8.8 ft-lbs of impact energy for hard-hitting performance in any concrete. For lighter applications, the two-speed impact mode allows you to reduce BPM to 2,200. Advanced constant power technology electronics and a mechanical clutch enhance your control and the rotary hammer's long-term durability. The anti-vibration system and side
Product Type	15 LB Sdsmax Demo Hammer
Special Features	14 AMP, 1,300 Mwo Milwaukee Motor- Provides Best In Class Power And Highest Overload Protection; 8.8 FT/LB Impact Energy- Heavy Duty Crank Piston Mechanism Delivers Hard Hitting Performance; 2 Speed Impact Mode- Low Reduces Beats Per Minute (2,200 BPM) For Light Materials; Constant Power Technology- Maintains Drilling Speed And Power When The Tool Is Under Load; Avs: Anti Vibration System- Actively Reduces User Vibration And Increases Productivity; Variable Position Chisel Stop- Fixes The Chisel In 12 Diff

## Manufacturer Information

Brand	Milwaukee Electric Tool
GTIN	00045242155521
Manufacturers Part Number	5446-21
UPC	045242155521

## Taxonomies, Classifications, and Categories

Category Description	POWER TOOLS
----------------------	-------------

## Trade Size

Amperage	14.0
----------	------

## Packaging

Carton	1
Weight Per each	25.25

## Uses, Certifications, and Standards

Application	For The Toughest Demolition Applications
-------------	--