



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



5662 Duplex Recp 15A 250V S+B Wire BR

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | 5662 |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Duplex Receptacle, 15 A, 250 V Ac, 2 Poles, 3 Wires, #14 to #10 Awg Compatible Wire Size, Back and Side Wired Connection, Wall Mount, 1.322 In Length, 0.780 In Width, 3.281 In Height, Nylon Material, Brown, 0.2100 LB |
| Weight per unit | 0.2083 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|---------------------|--|
| amperage rating | 15 |
| connection | Back and side wire |
| Dielectric Strength | Withstands 2000V minimum |
| Poles | Double Pole |
| Voltage | 250.0 V |
| Wattage | Electrical power is expressed in Amps and Volts. |
| Wire Size | 14 - 10 |

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | DUPLEX RECP 15A 250V S+B WIRE BR |
| extra long description | P&S 5662 RECP DUP 15A 250V S+B WIRE |

Manufacturer Information

| | |
|-------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007566208 |
| UPC | 785007566208 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Residential receptacles |
| Type | Spec Grade Receptacle, Heavy-Duty |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 10 |
| Package | 100 |
| Weight Per each | 0.2083 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Commercial |
| environmental conditions | Flammability: UL94 V2 |
| Mounting | WALL |
| standard | FEDSPEC, CULUS, cULus UL498, CSA C22.2 No. 42 |
| Temperature Rating | -40° - 60° C |