



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 691 Combo 15A 1 SW 1P-120V 1RECP-125V BR

*Pass & Seymour/Legrand*

Catalog Number	691
Manufacturer	Pass & Seymour/Legrand
Description	Our Standard Pass and Seymour Combination Switches Allow You to Add Lights to Any Room In Your Home Without Having to Add or Replace Wall Boxes.
Weight per unit	0.2171 (lbs/each)
Product Category	Combination Devices

### Features

action	SP & Recptacle
actuator	Toggle
amperage rating	15
connection	Side wire
Contact Configuration	N-O
Contact Rating	15 Amp, 120/125 VAC
indoor/outdoor	Indoor
Mounting Type	Box
Number of Switches	1.0
operating cycles	30k.0
Outlet Type	Indoor
package quantity	1.0
Poles	1
supply voltage	125.0
Voltage	120/125 V
Voltage Rating	120/125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Color	Brown
Finish	Matte

### Dimensions and Weight

Size	1.32 L x 0.94 W x 4.06 H
------	--------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	COMBO 15A 1 SW 1P-120V 1RECP-125V BR
extra long description	P&S 691 COMBO 15A 1 SW 1P-120V 1REC
Features	Combination
Long Description	Our standard Pass and Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes.
Product Type	Combo 15A 1 SW 1P-120V 1RECP-125V BN
Special Features	Easily accessible break-off for separate or common feed. Side wire #12 and #14 AWG. Two devices fit into the space of one. Grounding combination devices meet NEC Requirements.

## Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007691009
UPC	785007691009

## Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Switch, Outlet, Combination

## Trade Size

Amperage	15.0
----------	------

## Packaging

Carton	10
Package	50
Weight Per each	0.2171

## Uses, Certifications, and Standards

Application	Residential/Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
Operating Temperature	Maximum continuous +60°C, minimum -30°C
standard	CULUS, UL20, UL498