



COMBINATION SWITCHES

696WG | [Pass & Seymour](#)

FEATURES & BENEFITS

Single Pole, Three-Way Combination Switch, 15 amps, 120/277 volts, White.

- Easily accessible break-off separate or common feed.
- Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: White
Type: Combination, Double
Number Of Poles: 1, 3-way

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
UL Listing No: 20
UL Standard: Yes
UN SPSC: 39121407

DIMENSIONS

Depth (US): 0.94"
Height (US): 3.28"
Width (US): 1.32"

TECHNICAL INFORMATION

Amps: 17A
Volts: 120/277VAC
Volts (AC): 120/277

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant





COMBINATION SWITCHES

696WG | [Pass & Seymour](#)

FEATURES & BENEFITS

Single Pole, Three-Way Combination Switch, 15 amps, 120/277 volts, White.

- Easily accessible break-off separate or common feed.
- Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: White
Type: Combination, Double
Number Of Poles: 1, 3-way

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
UL Listing No: 20
UL Standard: Yes
UN SPSC: 39121407

DIMENSIONS

Depth (US): 0.94"
Height (US): 3.28"
Width (US): 1.32"

TECHNICAL INFORMATION

Amps: 17A
Volts: 120/277VAC
Volts (AC): 120/277

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

