

# ETP Raintight 700GSR Series Gland Compression Connectors

## Application

- To ground and secure EMT raceway to boxes and enclosures in wet conditions.

## Features

- UL Listed Raintight.
- Green compression nut identifies the fitting as raintight.
- No disassembly required.
- Male hub threads NPS.
- Available with and without insulated throat.
- Concretetight.

## Materials/Finish

- Body and nut: steel
- Knockout sealing ring: EPDM rubber
- Body and nut: zinc electroplate

## Certifications and Compliances

- UL Standard: 514B
- UL Listed: E-14895
- UL Listed Raintight



7100GSR



7100GSRT

Trade Size (Inches)	Dimensions in Millimeters (Inches)				Weight per 100 kg (lb)	Catalog Number	
	Body Length	Maximum Diameter	Thread Length	Without Insulated Throat		Insulated Throat	
1/2	36.6 (1.44)	27.9 (1.10)	8.6 (0.34)	4.5 (10)	7050GSR	7050GSRT	
3/4	38.1 (1.50)	34.5 (1.36)	8.6 (0.34)	6.8 (15)	7075GSR	7075GSRT	
1	44.5 (1.75)	34.5 (1.36)	9.9 (0.39)	10.0 (22)	7100GSR	7100GSRT	
1-1/4	50.8 (2.00)	52.6 (2.07)	10.2 (0.40)	16.3 (36)	7125GSR	7125GSRT	
1-1/2	50.8 (2.00)	58.7 (2.31)	10.2 (0.40)	18.1 (40)	7150GSR	7150GSRT	
2	58.9 (2.32)	70.9 (2.79)	10.4 (0.41)	24.5 (54)	7200GSR	7200GSRT	
2-1/2	91.9 (3.62)	92.2 (3.63)	16.5 (0.65)	68.0 (150)	7250GSR	7250GSRT	
3	95.3 (3.75)	109.0 (4.29)	16.5 (0.65)	83.9 (185)	7300GSR	7300GSRT	
3-1/2	97.8 (3.85)	121.9 (4.80)	18.3 (0.72)	97.5 (215)	7350GSR	7350GSRT	
4	99.1 (3.90)	133.9 (5.27)	18.3 (0.72)	108.0 (238)	7400GSR	7400GSRT	