



# Core & Coil (71A) MH 175W - 450W

## CORE & COIL HID 71A5770001D

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

### Product data

General Information	
ANSI Code	M58
Lamp Type	250W MH
Number of Lamps	1 piece/unit
Circuit Type	CWA
Ballast Type	Magnetic HID
Base Model	71A5770
Core Size	4 1/4 x 4 3/4 (2 coil)
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	NA
Ignitor Temperature Rating	NA
Capacitor Value	15 MFD
Capacitor Catalog Number	7C150P40R
Capacitor Requirements	400V
Capacitor Temperature Rating	105°C
Capacitor Diameter/Oval Dimensions	1.75 in
Capacitor Height	3.75 in
Automatic Restart	No
Operating and Electrical	
Input Voltage	120/208/240/277 V

Input Frequency	60 Hz
Input Current (Open Circuit)	1.7/1/0.85/0.75 A
Input Current (Starting)	2.2/1.3/1.1/1 A
Input Current (Short Circuit)	1.9-2.7/1.1-1.7/0.95-1.35/0.8-1.2 A
Secondary Short Circuit Current	2.25-2.75 A
Constant Wattage Deviation	10%
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Open Circuit Voltage	300 V
Input Current (Nom)	2.5/1.45/1.25/1.1 A A
Input Power (Nom)	298 W
Rated Lamp Power	250 W
Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes
Max Ballast-Lamp Distance Remote Wiring	Determined by AWG used
Recommended Fuse Value	8/5/5/3 A

## Core & Coil (71A) MH 175W - 450W

### Approval and Application

Open Circuit Voltage Test (Volts)	270-330 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	B/B/B/B
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029B

### Product Data

Order product name	CORE & COIL HID 71A5770001D
EAN/UPC - Product	781087096451
Order code	913700534809
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913700534809
Net Weight (Piece)	4.523 kg

### Dimensional drawing



MH BAL 250W M58 QUAD KIT

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 71A5770001D	3.15 in	1.6 in	4.8 in	4.4 in	4.3 in	3.9 in





# Core & Coil (71A) MH 175W - 450W

## CORE & COIL HID 71A5770001D

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

### Product data

General Information	
ANSI Code	M58
Lamp Type	250W MH
Number of Lamps	1 piece/unit
Circuit Type	CWA
Ballast Type	Magnetic HID
Base Model	71A5770
Core Size	4 1/4 x 4 3/4 (2 coil)
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	NA
Ignitor Temperature Rating	NA
Capacitor Value	15 MFD
Capacitor Catalog Number	7C150P40R
Capacitor Requirements	400V
Capacitor Temperature Rating	105°C
Capacitor Diameter/Oval Dimensions	1.75 in
Capacitor Height	3.75 in
Automatic Restart	No
Operating and Electrical	
Input Voltage	120/208/240/277 V

Input Frequency	60 Hz
Input Current (Open Circuit)	1.7/1/0.85/0.75 A
Input Current (Starting)	2.2/1.3/1.1/1 A
Input Current (Short Circuit)	1.9-2.7/1.1-1.7/0.95-1.35/0.8-1.2 A
Secondary Short Circuit Current	2.25-2.75 A
Constant Wattage Deviation	10%
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Open Circuit Voltage	300 V
Input Current (Nom)	2.5/1.45/1.25/1.1 A A
Input Power (Nom)	298 W
Rated Lamp Power	250 W
Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes
Max Ballast-Lamp Distance Remote Wiring	Determined by AWG used
Recommended Fuse Value	8/5/5/3 A

## Core & Coil (71A) MH 175W - 450W

### Approval and Application

Open Circuit Voltage Test (Volts)	270-330 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	B/B/B/B
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029B

### Product Data

Order product name	CORE & COIL HID 71A5770001D
EAN/UPC - Product	781087096451
Order code	913700534809
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913700534809
Net Weight (Piece)	4.523 kg

### Dimensional drawing



MH BAL 250W M58 QUAD KIT

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 71A5770001D	3.15 in	1.6 in	4.8 in	4.4 in	4.3 in	3.9 in

