


PHILIPS

Lighting



Core & Coil (71A) MH 175W - 450W

CORE & COIL HID 71A5750001D

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information		Input Frequency	
ANSI Code	M58	Input Current (Open Circuit)	2/1.2/1/0.9/0.5 A
Lamp Type	250W MH	Input Current (Starting)	2.4/1.4/1.2/1.05/0.6 A
Number of Lamps	1 piece/unit	Input Current (Short Circuit)	1.9-2.9/1.1-1.7/0.9-1.4/0.8-1.25/0.45-0.75 A
Circuit Type	CWA	Secondary Short Circuit Current	2.25-2.8 A
Ballast Type	Magnetic HID	Constant Wattage Deviation	10%
Base Model	71A5750	Ballast Factor (Nom)	1
Core Size	4 1/4 x 4 3/4 (2 coil)	Power Factor (Nom)	0.90
Suitable For Outdoor Use	Yes	Open Circuit Voltage	315 V
Ignitor Catalog Number	NA	Input Current (Nom)	2.6/1.5/1.4/1.1/0.65 A A
Ignitor Temperature Rating	NA	Input Power (Nom)	290 W
Capacitor Value	15 MFD	Rated Lamp Power	250 W
Capacitor Catalog Number	7C150P40R	Wiring	
Capacitor Requirements	400V	Wire Striplength	0.5 mm
Capacitor Temperature Rating	105°C	Wire Length by Color	12"
Capacitor Diameter/Oval Dimensions	1.75 in	Wire Type	Stranded
Capacitor Height	3.75 in	Remote Wiring Configuration Allowed	Yes
Automatic Restart	No	Max Ballast-Lamp Distance Remote Wiring	Determined by AWG used
Operating and Electrical		Recommended Fuse Value	8/5/5/3/2 A
Input Voltage	120/208/240/277/480 V		

Core & Coil (71A) MH 175W - 450W

Approval and Application

Open Circuit Voltage Test (Volts)	285-345 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	A/A/B/A/B
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029B

Product Data

Order product name	CORE & COIL HID 71A5750001D
EAN/UPC - Product	781087111789
Order code	913710413801
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913710413801
Net Weight (Piece)	0.010 kg

Dimensional drawing



MH BAL 250W M58 5-TAP KIT

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 71A5750001D	3.1 in	1.6 in	4.8 in	4.4 in	4.3 in	3.9 in



PHILIPS

Lighting



Core & Coil (71A) MH 175W - 450W

CORE & COIL HID 71A5750001D

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information		Input Frequency	
ANSI Code	M58	Input Frequency	60 Hz
Lamp Type	250W MH	Input Current (Open Circuit)	2/1.2/1/0.9/0.5 A
Number of Lamps	1 piece/unit	Input Current (Starting)	2.4/1.4/1.2/1.05/0.6 A
Circuit Type	CWA	Input Current (Short Circuit)	1.9-2.9/1.1-1.7/0.9-1.4/0.8-1.25/0.45-0.75 A
Ballast Type	Magnetic HID	Secondary Short Circuit Current	2.25-2.8 A
Base Model	71A5750	Constant Wattage Deviation	10%
Core Size	4 1/4 x 4 3/4 (2 coil)	Ballast Factor (Nom)	1
Suitable For Outdoor Use	Yes	Power Factor (Nom)	0.90
Ignitor Catalog Number	NA	Open Circuit Voltage	315 V
Ignitor Temperature Rating	NA	Input Current (Nom)	2.6/1.5/1.4/1.1/0.65 A A
Capacitor Value	15 MFD	Input Power (Nom)	290 W
Capacitor Catalog Number	7C150P40R	Rated Lamp Power	250 W
Capacitor Requirements	400V	Wiring	
Capacitor Temperature Rating	105°C	Wire Striplength	0.5 mm
Capacitor Diameter/Oval Dimensions	1.75 in	Wire Length by Color	12"
Capacitor Height	3.75 in	Wire Type	Stranded
Automatic Restart	No	Remote Wiring Configuration Allowed	Yes
Operating and Electrical		Max Ballast-Lamp Distance Remote Wiring	Determined by AWG used
Input Voltage	120/208/240/277/480 V	Recommended Fuse Value	8/5/5/3/2 A

Core & Coil (71A) MH 175W - 450W

Approval and Application

Open Circuit Voltage Test (Volts)	285-345 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	A/A/B/A/B
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029B

Product Data

Order product name	CORE & COIL HID 71A5750001D
EAN/UPC - Product	781087111789
Order code	913710413801
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913710413801
Net Weight (Piece)	0.010 kg

Dimensional drawing



MH BAL 250W M58 5-TAP KIT

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 71A5750001D	3.1 in	1.6 in	4.8 in	4.4 in	4.3 in	3.9 in

