



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



7813PMD 30A 3P 3 PH Ac MD, Nema 1 Enc *Pass & Seymour/LeGrand*

Catalog Number	7813PMD
Manufacturer	Pass & Seymour/LeGrand
Description	Ac Manual Motor Controller, Suitable As Motor Disconnect - 10KA @ 600VAC, 30A Max. Class J Fuse.
Weight per unit	0.7180 (lbs/each)
Product Category	Misc Wiring Devices

Features

actuator	Toggle
amperage rating	30
connection	Side & Back Wired
Enclosure Type	Nema 1
load	30A
operating cycles	50000
Poles	3
Voltage	600.0 V
Voltage Rating	600

Material, Color, and Finish

Color	Black
-------	-------

Dimensions and Weight

Size	2.8" Depth x 2.825" Width x 3.91" Height
------	--

Descriptions

Description	30A 3P 3 PH AC MD, NEMA 1 ENC
extra long description	P&S 7813PMD 30A 3P 3 PH AC MD, NEMA
Long Description	AC Manual Motor Controller, suitable as Motor Disconnect - 10KA @ 600VAC, 30A max. Class J Fuse.
Product Type	30A 3P 3 PH Ac MD, Nema 1 Enc
Special Features	Three Pole, Three Phase AC Manual Motor Controller, suitable as Motor Disconnect

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007267693
Manufacturers Part Number	7813PMD
UPC	785007267693

Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	Manual Controller



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Amperage 30.0

Packaging

Carton 1

Package 10

Weight Per each 0.718

Uses, Certifications, and Standards

Application Commercial/Industrial

Enclosure NEMA 1

environmental conditions UL94 V2

Frequency Rating 60Hz

Mounting FLUSH

Operating Temperature Maximum continuous +75°C, minimum -40°C

standard CULUS, CSA Listed, UL Listed