



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



7202 208-277V DPST 40A 24 Hour With Skip Day

Nsi Industries

| | |
|------------------|-------------------------------------|
| Catalog Number | 7202 |
| Manufacturer | Nsi Industries |
| Description | Tork 7202 24 Hour Skip A Day 40A 20 |
| Weight per unit | 2.4 (lbs/each) |
| Product Category | Wiring Devices |

Features

| | |
|----------------|--------------|
| action | DPST |
| Base | Screw |
| Contact Rating | 208-277 VAC |
| Number of Pins | 12 Pair |
| Phase | Single Phase |
| Poles | 2 |
| Timing Range | 24 Hour |

Dimensions and Weight

| | |
|------|-----------------------------|
| Size | L=4.687 - H=7.937 - W=2.937 |
|------|-----------------------------|

Descriptions

| | |
|------------------|--|
| Description | 208-277V DPST 40A 24 HOUR WITH SKIP DAY |
| Long Description | TORK 7202 24 Hour Skip A Day 40A 20 |
| Product Type | 24 Hour Skip A Day 40A 208-277V DPST |
| Special Features | DPST 24 Hour Time Switch With Skip-A-Day Feature |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00786261110022 |
| Manufacturers Part Number | 7202 |
| UPC | 786261110022 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | TIME CLOCKS |
| Type | 24 Hour Time Switch |

Availability

| | |
|---------------------|----------|
| Manufacturer Status | Inactive |
| Status | Inactive |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 2.4 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|---------------------|
| Application | NSI |
| Enclosure | NEMA 1 Metal Indoor |
| environmental conditions | -40 to 165 F |
| Frequency Rating | 60 Hz |
| Mounting | Screw Mount |
| Operating Temperature | -40 to 165 F |
| standard | UL-CSA |