





GE
Lighting

41865 - 7613

GE PAR36 - Emergency Building Light; Emergency Building



GENERAL CHARACTERISTICS

Lamp Type	Sealed Beam - PAR
Bulb	PAR36
Base	Screw Terminals
Filament	C-6
Rated Life	50.0 hrs
Primary Application	Emergency Building Light; Emergency Building

PHOTOMETRIC CHARACTERISTICS

Beam Spread - Horizontal	30.0 - 10.0 °
Beam Spread - Vertical	20.0 - 10.0 °
Max. Beam Candlepower (MBCP) (MAX)	400.0

ELECTRICAL CHARACTERISTICS

Wattage	8.0
Voltage	6.0

DIMENSIONS

Maximum Overall Length (MOL)	2.7500 in(69.8 mm)
Bulb Diameter (DIA)	4.500 in(114.3 mm)

PRODUCT INFORMATION



Product Code	41865
Description	7613
ANSI Code	7613
Standard Package	Case
Standard Package GTIN	00043168418652
Standard Package Quantity	12
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	12
UPC	043168962278



GE
Lighting

41865 - 7613

GE PAR36 - Emergency Building Light; Emergency Building



GENERAL CHARACTERISTICS

Lamp Type	Sealed Beam - PAR
Bulb	PAR36
Base	Screw Terminals
Filament	C-6
Rated Life	50.0 hrs
Primary Application	Emergency Building Light; Emergency Building

PHOTOMETRIC CHARACTERISTICS

Beam Spread - Horizontal	30.0 - 10.0 °
Beam Spread - Vertical	20.0 - 10.0 °
Max. Beam Candlepower (MBCP) (MAX)	400.0

ELECTRICAL CHARACTERISTICS

Wattage	8.0
Voltage	6.0

DIMENSIONS

Maximum Overall Length (MOL)	2.7500 in(69.8 mm)
Bulb Diameter (DIA)	4.500 in(114.3 mm)

PRODUCT INFORMATION

Product Code	41865
Description	7613
ANSI Code	7613
Standard Package	Case
Standard Package GTIN	00043168418652
Standard Package Quantity	12
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	12
UPC	043168962278