



Safety Data Sheet

Copyright,2017,3M Company.

All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

Document Group:	26-5243-6	Version Number:	3.04
Issue Date:	02/15/17	Supersedes Date:	07/14/16

Product identifier

7620-T-X-3G AND 7690-T-X-3G SERIES QT-III 3 CONDUCTOR TERMINATION KITS (tubular series)

ID Number(s):

80-6112-0264-1, 80-6112-0265-8, 80-6112-0266-6, 80-6112-0267-4, 80-6112-0268-2, 80-6112-0269-0, 80-6112-0270-8, 80-6112-0271-6, 80-6112-0273-2, 80-6112-0274-0, 80-6112-0275-7, 80-6112-0276-5

Recommended use

Electrical

Supplier's details

MANUFACTURER:	3M
DIVISION:	Electrical Markets Division
ADDRESS:	3M Center, St. Paul, MN 55144-1000, USA
Telephone:	1-888-3M HELPS (1-888-364-3577)

Emergency telephone number

1-800-364-3577 or (651) 737-6501 (24 hours)

This product is a kit or a multipart product which consists of multiple, independently packaged components. A Safety Data Sheet (SDS), Article Information Sheet (AIS), or Article Information Letter (AIL) for each of these components is included. Please do not separate the component documents from this cover page. The document numbers for components of this product are:

26-2852-7

Reason for Reissue

Conversion to GHS format SDS.

DISCLAIMER: The information in this Safety Data Sheet (SDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the SDS available directly from 3M

3M USA SDSs are available at www.3M.com



Safety Data Sheet

Copyright, 2018, 3M Company.

All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

Document Group:	26-2852-7	Version Number:	3.03
Issue Date:	02/15/18	Supersedes Date:	01/18/18

SECTION 1: Identification

1.1. Product identifier

3M™ Cable Preparation Kit CC-2 (Can)

Product Identification Numbers

ID Number	UPC	ID Number	UPC
78-8061-7605-9		78-8127-6979-8	
80-6105-9299-2		80-6112-0013-2	
80-6114-2769-3			

1.2. Recommended use and restrictions on use

Recommended use

Electrical, SOLVENT SOAKED PADS FOR CLEANING CABLE

1.3. Supplier's details

MANUFACTURER:	3M
DIVISION:	Electrical Markets Division
ADDRESS:	3M Center, St. Paul, MN 55144-1000, USA
Telephone:	1-888-3M HELPS (1-888-364-3577)

1.4. Emergency telephone number

1-800-364-3577 or (651) 737-6501 (24 hours)

SECTION 2: Hazard identification

2.1. Hazard classification

Flammable Liquid: Category 4.
 Skin Corrosion/Irritation: Category 2.
 Skin Sensitizer: Category 1.
 Specific Target Organ Toxicity (single exposure): Category 3.

2.2. Label elements

Signal word

Warning

Symbols

Exclamation mark |

Pictograms



Hazard Statements

Combustible liquid.

Causes skin irritation.

May cause an allergic skin reaction.

May cause drowsiness or dizziness.

Precautionary Statements

Prevention:

Keep away from heat/sparks/open flames/hot surfaces. - No smoking.

Avoid breathing dust/fume/gas/mist/vapors/spray.

Use only outdoors or in a well-ventilated area.

Wear protective gloves.

Wash thoroughly after handling.

Contaminated work clothing must not be allowed out of the workplace.

Response:

IF INHALED: Remove person to fresh air and keep comfortable for breathing.

IF ON SKIN: Wash with plenty of soap and water.

If skin irritation or rash occurs: Get medical advice/attention.

Take off contaminated clothing and wash it before reuse.

Call a POISON CENTER or doctor/physician if you feel unwell.

In case of fire: Use a fire fighting agent suitable for flammable liquids such as dry chemical or carbon dioxide to extinguish.

Storage:

Store in a well-ventilated place. Keep container tightly closed.

Keep cool.

Store locked up.

Disposal:

Dispose of contents/container in accordance with applicable local/regional/national/international regulations.

SECTION 3: Composition/information on ingredients

Ingredient	C.A.S. No.	% by Wt
Isoparaffinic Hydrocarbon	64742-48-9	50 - 70
Cotton pads	None	25 - 40
D-LIMONENE	5989-27-5	5 - 20

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

Remove person to fresh air. If you feel unwell, get medical attention.

Skin Contact:

Immediately wash with soap and water. Remove contaminated clothing and wash before reuse. If signs/symptoms develop, get medical attention.

Eye Contact:

No need for first aid is anticipated.

If Swallowed:

Rinse mouth. If you feel unwell, get medical attention.

4.2. Most important symptoms and effects, both acute and delayed

See Section 11.1. Information on toxicological effects.

4.3. Indication of any immediate medical attention and special treatment required

Not applicable

SECTION 5: Fire-fighting measures**5.1. Suitable extinguishing media**

In case of fire: Use a fire fighting agent suitable for flammable liquids such as dry chemical or carbon dioxide to extinguish.

5.2. Special hazards arising from the substance or mixture

Closed containers exposed to heat from fire may build pressure and explode.

5.3. Special protective actions for fire-fighters

Water may not effectively extinguish fire; however, it should be used to keep fire-exposed containers and surfaces cool and prevent explosive rupture. Wear full protective clothing, including helmet, self-contained, positive pressure or pressure demand breathing apparatus, bunker coat and pants, bands around arms, waist and legs, face mask, and protective covering for exposed areas of the head.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Evacuate area. Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Use only non-sparking tools. Ventilate the area with fresh air. For large spill, or spills in confined spaces, provide mechanical ventilation to disperse or exhaust vapors, in accordance with good industrial hygiene practice. Warning! A motor could be an ignition source and could cause flammable gases or vapors in the spill area to burn or explode. Refer to other sections of this SDS for information regarding physical and health hazards, respiratory protection, ventilation, and personal protective equipment.

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Contain spill. Cover spill area with a fire-extinguishing foam. An appropriate aqueous film forming foam (AFFF) is recommended. Remember, adding an absorbent material does not remove a physical, health, or environmental hazard. Collect as much of the spilled material as possible using non-sparking tools. Place in a metal container approved for transportation by appropriate authorities. Clean up residue with an appropriate solvent selected by a qualified and authorized person. Ventilate the area with fresh air. Read and follow safety precautions on the solvent label and SDS. Seal the container. Dispose of collected material as soon as possible in accordance with applicable local/regional/national/international regulations.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

For industrial or professional use only. Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Avoid breathing dust/fume/gas/mist/vapors/spray. Do not get in eyes, on skin, or on clothing. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace. Avoid release to the environment. Wash contaminated clothing before reuse. Avoid contact with oxidizing agents (eg. chlorine, chromic acid etc.)

7.2. Conditions for safe storage including any incompatibilities

Store in a well-ventilated place. Keep container tightly closed. Keep cool. Protect from sunlight. Store away from heat. Store away from acids. Store away from oxidizing agents.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limits

No occupational exposure limit values exist for any of the components listed in Section 3 of this SDS.

8.2. Exposure controls

8.2.1. Engineering controls

No engineering controls required.

8.2.2. Personal protective equipment (PPE)

Eye/face protection

Under normal use conditions, eye exposure is not expected to be significant enough to require eye protection.

Skin/hand protection

Select and use gloves and/or protective clothing approved to relevant local standards to prevent skin contact based on the results of an exposure assessment. Selection should be based on use factors such as exposure levels, concentration of the substance or mixture, frequency and duration, physical challenges such as temperature extremes, and other use conditions. Consult with your glove and/or protective clothing manufacturer for selection of appropriate compatible gloves/protective clothing. Note: Nitrile gloves may be worn over polymer laminate gloves to improve dexterity.

Gloves made from the following material(s) are recommended: Nitrile Rubber

Polymer laminate

If this product is used in a manner that presents a higher potential for exposure (eg. spraying, high splash potential etc.), then use of protective coveralls may be necessary. Select and use body protection to prevent contact based on the results of an exposure assessment. The following protective clothing material(s) are recommended: Apron – Nitrile

Apron - polymer laminate

Respiratory protection

An exposure assessment may be needed to decide if a respirator is required. If a respirator is needed, use respirators as part of a full respiratory protection program. Based on the results of the exposure assessment, select from the following respirator type(s) to reduce inhalation exposure:

Half facepiece or full facepiece air-purifying respirator suitable for organic vapors

For questions about suitability for a specific application, consult with your respirator manufacturer.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

General Physical Form:	Solid (Lint-free cloths soaked with liquid)
Specific Physical Form:	Cloth pads soaked in liquid in can or bag
Odor, Color, Grade:	citrus-like odor
Odor threshold	<i>No Data Available</i>
pH	7
Melting point	<i>No Data Available</i>
Boiling Point	380 °F - 480 °F
Flash Point	144 °F [<i>Test Method</i> :Closed Cup]
Evaporation rate	<i>No Data Available</i>
Flammability (solid, gas)	Not Classified
Flammable Limits(LEL)	<i>No Data Available</i>
Flammable Limits(UEL)	<i>No Data Available</i>
Vapor Pressure	< 1 mmHg [@ 25 °C]
Vapor Density	> 1 [<i>Ref Std</i> :AIR=1]
Density	0.76 g/ml
Specific Gravity	0.76 [<i>Ref Std</i> :WATER=1]
Solubility in Water	Nil
Solubility- non-water	<i>No Data Available</i>
Partition coefficient: n-octanol/ water	<i>No Data Available</i>
Autoignition temperature	<i>No Data Available</i>
Decomposition temperature	<i>No Data Available</i>
Viscosity	1.5 centipoise
Molecular weight	<i>No Data Available</i>
Volatile Organic Compounds	Approximately 740 g/l
VOC Less H2O & Exempt Solvents	760 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

This material may be reactive with certain agents under certain conditions - see the remaining headings in this section.

10.2. Chemical stability

Stable.

10.3. Possibility of hazardous reactions

Hazardous polymerization will not occur.

10.4. Conditions to avoid

Sparks and/or flames

10.5. Incompatible materials

Strong oxidizing agents

10.6. Hazardous decomposition products

<u>Substance</u>	<u>Condition</u>
Carbon monoxide	Not Specified
Carbon dioxide	Not Specified

SECTION 11: Toxicological information

The information below may not be consistent with the material classification in Section 2 if specific ingredient classifications are mandated by a competent authority. In addition, toxicological data on ingredients may not be reflected in the material classification and/or the signs and symptoms of exposure, because an ingredient may be present below the threshold for labeling, an ingredient may not be available for exposure, or the data may not be relevant to the material as a whole.

11.1. Information on Toxicological effects

Signs and Symptoms of Exposure

Based on test data and/or information on the components, this material may produce the following health effects:

Inhalation:

May be harmful if inhaled.

Respiratory Tract Irritation: Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

May cause additional health effects (see below).

Skin Contact:

Skin Irritation: Signs/symptoms may include localized redness, swelling, itching, dryness, cracking, blistering, and pain.

Allergic Skin Reaction (non-photo induced): Signs/symptoms may include redness, swelling, blistering, and itching.

Eye Contact:

Contact with the eyes during product use is not expected to result in significant irritation.

Ingestion:

Physical Blockage: Signs/symptoms may include cramping, abdominal pain, and constipation.

Gastrointestinal Irritation: Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhea.

May cause additional health effects (see below).

Additional Health Effects:

Single exposure may cause target organ effects:

Central Nervous System (CNS) Depression: Signs/symptoms may include headache, dizziness, drowsiness, incoordination, nausea, slowed reaction time, slurred speech, giddiness, and unconsciousness.

Toxicological Data

If a component is disclosed in section 3 but does not appear in a table below, either no data are available for that endpoint or the data are not sufficient for classification.

Acute Toxicity

Name	Route	Species	Value
Overall product	Dermal		No data available; calculated ATE >5,000 mg/kg
Overall product	Inhalation-Vapor(4 hr)		No data available; calculated ATE ₂₀ - 50 mg/l
Overall product	Ingestion		No data available; calculated ATE >5,000 mg/kg
Isoparaffinic Hydrocarbon	Inhalation-Vapor		LC ₅₀ estimated to be 20 - 50 mg/l
Isoparaffinic Hydrocarbon	Dermal	Rabbit	LD ₅₀ > 3,000 mg/kg
Isoparaffinic Hydrocarbon	Ingestion	Rat	LD ₅₀ > 5,000 mg/kg
D-LIMONENE	Inhalation-Vapor (4	Mouse	LC ₅₀ > 3.14 mg/l

	hours)		
D-LIMONENE	Dermal	Rabbit	LD50 > 5,000 mg/kg
D-LIMONENE	Ingestion	Rat	LD50 4,400 mg/kg

ATE = acute toxicity estimate

Skin Corrosion/Irritation

Name	Species	Value
Isoparaffinic Hydrocarbon	Rabbit	Irritant
D-LIMONENE	Rabbit	Mild irritant

Serious Eye Damage/Irritation

Name	Species	Value
Isoparaffinic Hydrocarbon	Rabbit	No significant irritation
D-LIMONENE	Rabbit	Mild irritant

Skin Sensitization

Name	Species	Value
Isoparaffinic Hydrocarbon	Guinea pig	Not classified
D-LIMONENE	Mouse	Sensitizing

Respiratory Sensitization

For the component/components, either no data are currently available or the data are not sufficient for classification.

Germ Cell Mutagenicity

Name	Route	Value
Isoparaffinic Hydrocarbon	In vivo	Not mutagenic
Isoparaffinic Hydrocarbon	In Vitro	Some positive data exist, but the data are not sufficient for classification
D-LIMONENE	In Vitro	Not mutagenic
D-LIMONENE	In vivo	Not mutagenic

Carcinogenicity

Name	Route	Species	Value
Isoparaffinic Hydrocarbon	Dermal	Mouse	Some positive data exist, but the data are not sufficient for classification
Isoparaffinic Hydrocarbon	Inhalation	Human and animal	Some positive data exist, but the data are not sufficient for classification
D-LIMONENE	Ingestion	Rat	Some positive data exist, but the data are not sufficient for classification

Reproductive Toxicity

Reproductive and/or Developmental Effects

Name	Route	Value	Species	Test Result	Exposure Duration
Isoparaffinic Hydrocarbon	Inhalation	Not classified for development	Rat	NOAEL 2.4 mg/l	during organogenesis
D-LIMONENE	Ingestion	Not classified for female reproduction	Rat	NOAEL 750 mg/kg/day	prematuring & during gestation
D-LIMONENE	Ingestion	Not classified for development	Multiple animal species	NOAEL 591 mg/kg/day	during organogenesis

Target Organ(s)

Specific Target Organ Toxicity - single exposure

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
Isoparaffinic Hydrocarbon	Inhalation	central nervous system depression	May cause drowsiness or dizziness	Human and animal	NOAEL Not available	
Isoparaffinic Hydrocarbon	Inhalation	respiratory irritation	Some positive data exist, but the data are not sufficient for classification		NOAEL Not available	
Isoparaffinic Hydrocarbon	Inhalation	nervous system	Not classified	Dog	NOAEL 6.5 mg/l	4 hours
Isoparaffinic Hydrocarbon	Ingestion	central nervous system depression	May cause drowsiness or dizziness	Professional judgement	NOAEL Not available	
D-LIMONENE	Ingestion	nervous system	Not classified		NOAEL Not available	

Specific Target Organ Toxicity - repeated exposure

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
Isoparaffinic Hydrocarbon	Inhalation	nervous system	Not classified	Rat	LOAEL 4.6 mg/l	6 months
Isoparaffinic Hydrocarbon	Inhalation	kidney and/or bladder	Not classified	Rat	LOAEL 1.9 mg/l	13 weeks
Isoparaffinic Hydrocarbon	Inhalation	respiratory system	Not classified	Multiple animal species	NOAEL 0.6 mg/l	90 days
Isoparaffinic Hydrocarbon	Inhalation	bone, teeth, nails, and/or hair blood liver muscles	Not classified	Rat	NOAEL 5.6 mg/l	12 weeks
Isoparaffinic Hydrocarbon	Inhalation	heart	Not classified	Multiple animal species	NOAEL 1.3 mg/l	90 days
D-LIMONENE	Ingestion	kidney and/or bladder	Not classified	Rat	LOAEL 75 mg/kg/day	103 weeks
D-LIMONENE	Ingestion	liver	Not classified	Mouse	NOAEL 1,000 mg/kg/day	103 weeks
D-LIMONENE	Ingestion	heart endocrine system bone, teeth, nails, and/or hair hematopoietic system immune system muscles nervous system respiratory system	Not classified	Rat	NOAEL 600 mg/kg/day	103 weeks

Aspiration Hazard

Name	Value
Isoparaffinic Hydrocarbon	Aspiration hazard
D-LIMONENE	Aspiration hazard

Please contact the address or phone number listed on the first page of the SDS for additional toxicological information on this material and/or its components.

SECTION 12: Ecological information**Ecotoxicological information**

Please contact the address or phone number listed on the first page of the SDS for additional ecotoxicological information on this material and/or its components.

Chemical fate information

Please contact the address or phone number listed on the first page of the SDS for additional chemical fate information on this material and/or its components.

SECTION 13: Disposal considerations

13.1. Disposal methods

Dispose of contents/ container in accordance with the local/regional/national/international regulations.

Incinerate in a permitted waste incineration facility. Proper destruction may require the use of additional fuel during incineration processes. As a disposal alternative, Dispose of waste product in a permitted industrial waste facility. Empty drums/barrels/containers used for transporting and handling hazardous chemicals (chemical substances/mixtures/preparations classified as Hazardous as per applicable regulations) shall be considered, stored, treated & disposed of as hazardous wastes unless otherwise defined by applicable waste regulations. Consult with the respective regulating authorities to determine the available treatment and disposal facilities.

EPA Hazardous Waste Number (RCRA): Not regulated

SECTION 14: Transport Information

For Transport Information, please visit <http://3M.com/Transportinfo> or call 1-800-364-3577 or 651-737-6501.

SECTION 15: Regulatory information

15.1. US Federal Regulations

Contact 3M for more information.

EPCRA 311/312 Hazard Classifications:

Physical Hazards

Flammable (gases, aerosols, liquids, or solids)

Health Hazards

Respiratory or Skin Sensitization

Skin Corrosion or Irritation

Specific target organ toxicity (single or repeated exposure)

15.2. State Regulations

Contact 3M for more information.

15.3. Chemical Inventories

The components of this material are in compliance with the provisions of Australia National Industrial Chemical Notification and Assessment Scheme (NICNAS). Certain restrictions may apply. Contact the selling division for additional information.

The components of this product are in compliance with the new substance notification requirements of CEPA.

The components of this material are in compliance with the China "Measures on Environmental Management of New Chemical Substance". Certain restrictions may apply. Contact the selling division for additional information.

The components of this material are in compliance with the provisions of the Korean Toxic Chemical Control Law. Certain restrictions may apply. Contact the selling division for additional information.

The components of this material are in compliance with the provisions of Philippines RA 6969 requirements. Certain restrictions may apply. Contact the selling division for additional information.

The components of this product are in compliance with the chemical notification requirements of TSCA.

Contact 3M for more information.

15.4. International Regulations

Contact 3M for more information.

This SDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

SECTION 16: Other information

NFPA Hazard Classification

Health: 2 **Flammability:** 2 **Instability:** 0 **Special Hazards:** None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

HMIS Hazard Classification

Health: *2 **Flammability:** 2 **Physical Hazard:** 0 **Personal Protection:** B

Hazardous Material Identification System (HMIS® IV) hazard ratings are designed to inform employees of chemical hazards in the workplace. These ratings are based on the inherent properties of the material under expected conditions of normal use and are not intended for use in emergency situations. HMIS® IV ratings are to be used with a fully implemented HMIS® IV program. HMIS® is a registered mark of the American Coatings Association (ACA).

Document Group:	26-2852-7	Version Number:	3.03
Issue Date:	02/15/18	Supersedes Date:	01/18/18

Reason for Reissue

Conversion to GHS format SDS.

DISCLAIMER: The information in this Safety Data Sheet (SDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the SDS available directly from 3M.

3M USA SDSs are available at www.3M.com