



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 870LAG Radiant Switch 1P 15A 120/277V La

*Pass & Seymour/Legrand*

Catalog Number	870LAG
Manufacturer	Pass & Seymour/Legrand
Description	Decorator Switch, Single Pole, Grounding, In Light Almond. It Has A Designer-Style Satin-Finish Rocker With A Smooth, Quiet Paddle Action. It Is Made With High-Impact Resistant Thermoplastic Construction. 15AMP 120/277V.
Weight per unit	0.1400 (lbs/each)
Product Category	Gen Purpose Switches

### Features

gang	1
insulation	Bare
Material	Thermoplastic
media	Yes
Mounting Type	Box
Number of Gangs	1.0
Number of Switches	1.0
Poles	Single Pole
Switch Type	Paddle
Voltage	120/277 V

### Material, Color, and Finish

Color	Light Almond
-------	--------------

### Dimensions and Weight

Size	4.2 in
Thickness	1.5 in

### Descriptions

Description	RADIANT SWITCH 1P 15A 120/277V LA
extra long description	P&S TM870LA RADIANT SWITCH 1P 15A 1
Long Description	Decorator Switch, single pole, grounding, in light almond. It has a designer-style satin-finish rocker with a smooth, quiet paddle action. It is made with high-impact resistant thermoplastic construction. 15Amp 120/277V.
Product Type	Radiant Switch 1P 15A 120/277V La
Special Features	Designer style, smooth quiet paddle action



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007245394
Manufacturers Part Number	TM870LA
UPC	785007245394

## Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	SWITCH

## Trade Size

Amperage	15.0
----------	------

## Packaging

Carton	10
Package	100
Weight Per each	0.14

## Uses, Certifications, and Standards

Application	Residential/Commercial
Mounting standard	WALL CULUS, UL, UL 498, 20