Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



834TZ 1-1/4" Plastic Bushing

Topaz - Southwire LLC

Catalog Number	834TZ
Manufacturer	Topaz - Southwire LLC
Description	Rigid Conduit Insulating Bushing, Threaded Female Type; Thermoplastic Material; 0.56 Inch; Imc/Rigid Conduit Used On; Ul, Csa Approval; 1.96 Inch Diameter; 105 Deg C Temperature Rating; 250 Per Case Standard Package; 1-1/4 Inch Trade Size
Weight per unit	N/A
Product Category	Plastic

Features

Material	Thermoplastic
Throat Type	PLASTIC INSULATED

Dimensions and Weight

Diameter	1.96 INCH
Height	0.56 INCH

Descriptions

Commodity Description	Rigid Conduit Fittings - Plastic
Description	1-1/4" PLASTIC BUSHING
extra long description	FEMALE THREADED TYPE; THERMOPLASTIC MATERIAL; 0.56 INCH; IMC/RIGID CONDUIT USED ON; UL (CANADA AND US) APPROVAL; 1.96 INCH DIAMETER; 105 DEG C TEMPERATURE RATING; 250 PER CASE STANDARD PACKAGE; 1-1/4 INCH TRADE SIZE; PLASTIC INSULATED THROAT TYPE; APPLICATION INDOOR, OUTDOOR
Long Description	RIGID CONDUIT INSULATING BUSHING, THREADED FEMALE TYPE; THERMOPLASTIC MATERIAL; 0.56 INCH; IMC/RIGID CONDUIT USED ON; UL, CSA APPROVAL; 1.96 INCH DIAMETER; 105 DEG C TEMPERATURE RATING; 250 PER CASE STANDARD PACKAGE; 1-1/4 INCH TRADE SIZE
Product Type	Rigid Conduit Insulating Bushing

Manufacturer Information

Brand	SOUTHWIRE ROUGH ELECTRICAL COMPONENTS
GTIN	00751338184800
Manufacturers Part Number	834TZ
UPC	751338184800

Taxonomies, Classifications, and Categories

Category Description	COUPLINGS, ADAPTERS, REDUCERS, BUSHINGS, & CAPS
Type	THREADED FEMALE

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Trade Size	1-1/4 INCH

Packaging

Carton	1
Package	25
Standard Package	250 PER CASE
Weight Per each	0

Uses, Certifications, and Standards

Approval	UL, CSA
Temperature Rating	105 DEG C
Used On	IMC/RIGID CONDUIT