



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



873G Radiant Switch 3W 15A 120/277V BN *Pass & Seymour/Legrand*

| | |
|------------------|--|
| Catalog Number | 873G |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Decorator SWITCH3WAY 15AMP 120/277V Grounding, Brown |
| Weight per unit | 0.1400 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|-------------|---------------|
| gang | 3 |
| insulation | Bare |
| Material | Thermoplastic |
| media | Yes |
| orientation | Vertical |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Brown |
|-------|-------|

Dimensions and Weight

| | |
|-----------|------|
| Size | 5" |
| Thickness | 1.8" |

Descriptions

| | |
|------------------------|--|
| Description | RADIANT SWITCH 3W 15A 120/277V BN |
| extra long description | P&S TM873 RADIANT SWITCH 3W 15A 120 |
| Long Description | Decorator Switch3Way 15Amp 120/277V Grounding, Brown |
| Product Type | Radiant Switch 3W 15A 120/277V BN |
| Special Features | Impact resistant nylon face, corrosion-resistant, plated steel strap, tamper resistant, heavy-duty |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007245417 |
| Manufacturers Part Number | TM873 |
| UPC | 785007245417 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | Residential Switches |
| Type | Combination switch |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.14 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|------------------------|
| Application | Residential/Commercial |
| Mounting | WALL |
| standard | UL 20 |