

Specifications

GENERAL

H-STRUT General Fittings are designed to fit with all H-STRUT 1⁵/₈" wide channels. All H-STRUT fittings are manufactured from 1/4" thick carbon steel, 1⁵/₈" wide, all holes are 9/16" diameter, spaced 1⁷/₈" on center and 1³/₁₆" from the end.

The more popular fittings are illustrated on the following pages. However, there are hundreds of other fittings available. Please contact the factory for any other fittings you may need for specific applications.

ORDERING

Please specify catalog number and finish.

MATERIAL

H-STRUT fittings are manufactured from the following material:

- Hot Rolled Steel SheetASTM A-1011
- Cold Rolled Steel SheetASTM A-1008
- Stainless Steel-Type 304/316.ASTM A-240
- Aluminum Fitting.ASTM B-221

FINISHES

H-STRUT fittings are available in the following finishes: (See technical section for additional information)


- Electro GalvanizedASTM B-633
- Hot Dipped GalvanizedASTM A-123
- Zinc Trivalent ChromiumASTM B-633-85
- Powder Coated Supr-Green.ASTM B-117
- PVC Coating - Available Upon Request

ANGLE BRACKETS

A-311

Four Hole Angle


Wt. 78#/C



A-312

Four Hole 90°
T-Plate Angle

Wt. 77#/C




A-318-L (left hand)

A-318-R (right hand shown)

Shelf Bracket


Wt. 138#/C



A-335

Universal Shelf
Bracket

Wt. 132#/C




A-330-L (left hand)

A-330-R (right hand shown)

Three Hole
90° Angle


Wt. 54#/C



A-307


Three Hole Angle
Bracket

Wt. 57#/C



Page Notes: 1/4" thick, 1 5/8" wide, holes 9/16" dia., spaced 1 7/8" on center and 1 3/16" from end.

Finish: Electro-galvanized



Specifications

GENERAL

H-STRUT General Fittings are designed to fit with all H-STRUT 1⁵/₈" wide channels. All H-STRUT fittings are manufactured from 1/4" thick carbon steel, 1⁵/₈" wide, all holes are 9/16" diameter, spaced 1⁷/₈" on center and 1³/₁₆" from the end.

The more popular fittings are illustrated on the following pages. However, there are hundreds of other fittings available. Please contact the factory for any other fittings you may need for specific applications.

ORDERING

Please specify catalog number and finish.

MATERIAL

H-STRUT fittings are manufactured from the following material:

- Hot Rolled Steel SheetASTM A-1011
- Cold Rolled Steel SheetASTM A-1008
- Stainless Steel-Type 304/316.ASTM A-240
- Aluminum Fitting.ASTM B-221

FINISHES

H-STRUT fittings are available in the following finishes: (See technical section for additional information)


- Electro GalvanizedASTM B-633
- Hot Dipped GalvanizedASTM A-123
- Zinc Trivalent ChromiumASTM B-633-85
- Powder Coated Supr-Green.ASTM B-117
- PVC Coating - Available Upon Request

ANGLE BRACKETS

A-311

Four Hole Angle


Wt. 78#/C



A-312

Four Hole 90°
T-Plate Angle

Wt. 77#/C




A-318-L (left hand)

A-318-R (right hand shown)

Shelf Bracket


Wt. 138#/C



A-335

Universal Shelf
Bracket

Wt. 132#/C




A-330-L (left hand)

A-330-R (right hand shown)

Three Hole
90° Angle


Wt. 54#/C



A-307

Three Hole Angle
Bracket

Wt. 57#/C



Page Notes: 1/4" thick, 1 5/8" wide, holes 9/16" dia., spaced 1 7/8" on center and 1 3/16" from end.

Finish: Electro-galvanized