



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



897720 Variable Temperature Heat Gun

Milwaukee Electric Tool

Catalog Number	897720
Manufacturer	Milwaukee Electric Tool
Description	Easily Dial In Your Preferred Temperature Setting From 100 to 1040 Degrees With The Milwaukee 11.6 Amp Variable Temperature Heat Gun. The Stay-Cool Handle and Heat Shield Protect You While The Gun'S Flameless Heat Takes Aim At Your Project. This Ergonomically Designed Tool Is Perfect For Shrink-Wrapping, Drying Paint, Thawing Pipes, Welding Plastics, Bending PVC Pipes and More.
Weight per unit	2.7 (lbs/each)
Product Category	Power Tools - Corded

Features

Cord Length	8.0
maximum temperature	1040
Voltage	120.0

Material, Color, and Finish

Housing Material	Glass-filled Nylon
------------------	--------------------

Dimensions and Weight

Length	10.5
--------	------

Descriptions

Description	VARIABLE TEMPERATURE HEAT GUN
extra long description	MILW 8977-20 Heat Gun
Features	Variable Temperature Heat Gun
Long Description	Easily dial in your preferred temperature setting from 100 to 1040 degrees with the Milwaukee 11.6 amp variable temperature heat gun. The stay-cool handle and heat shield protect you while the gun's flameless heat takes aim at your project. This ergonomically designed tool is perfect for shrink-wrapping, drying paint, thawing pipes, welding plastics, bending PVC pipes and more.
Product Type	Heat Gun

Manufacturer Information

Brand	Milwaukee®
GTIN	00045242062881
Manufacturers Part Number	8977-20
UPC	045242062881

Taxonomies, Classifications, and Categories

Category Description	POWER TOOLS
----------------------	-------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Amperage 11.6

Packaging

Carton 1

Package 5

Weight Per each 2.66