



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AGC12 12A 250V 1/4X1-1/4 Non-Rohs Fa Glass Fuse *Bussmann Fuses*

| | |
|------------------|--|
| Catalog Number | AGC12 |
| Manufacturer | Bussmann Fuses |
| Description | 2/10A 125V 3AG - 1/4" X 1-1/4" Glass, Fast Acting Fuse |
| Weight per unit | 0.0060 (lbs/each) |
| Product Category | Tools & Testers |

Features

| | |
|--------------------|---|
| amperage rating | 12 Amp |
| connection | Ferrule End X Ferrule End |
| Response Time | 60 Min Maximum at 135%, 120 S Maximum at 200% |
| type of indicators | Non-Indicating |
| Voltage Rating | 250 VAC |

Dimensions and Weight

| | |
|------|-----------------------------------|
| Size | 1/4 In Diameter X 1-1/4 In Length |
|------|-----------------------------------|

Descriptions

| | |
|------------------------|--|
| Description | 12A 250V 1/4X1-1/4 NON-ROHS FA GLASS FUSE |
| extra long description | EFSE AGC-12 BUSS SMALL DIMENSION FU |
| Long Description | 2/10A 125V 3AG - 1/4" x 1-1/4" Glass, Fast Acting Fuse |
| Product Type | Buss Small Dimension Fuse 5N Auto Pack |
| Special Features | Interrupt Rating 35 Amp at 250 Vac, 1000 Amp at 32 Vac, Material Glass Tube, Nickel Plated Brass Endcap |

Manufacturer Information

| | |
|---------------------------|-------------------------------|
| Brand | Cooper Bussmann North America |
| GTIN | 00051712703789 |
| Manufacturers Part Number | AGC-12 |
| UPC | 051712703789 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------|
| Category Description | GLASS FUSES (and ceramic) |
| Type | Electronic, Fast Acting |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|

Packaging

| | |
|-----------------|-------|
| Carton | 5 |
| Weight Per each | 0.006 |

Uses, Certifications, and Standards

| | |
|-------------|---------------------|
| Application | Electronic Circuits |
| standard | UL 248-14, CSA, CE |