



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## AFB0ELDWHGXDUVOL Led Egress Emgcy White

*Lithonia Lighting*

Catalog Number	AFB0ELDWHGXDUVOL
Manufacturer	Lithonia Lighting
Description	The Affinity® Afb Led Emergency Light By Lithonia Lighting® Is Stylish and Equally Durable For Indoor and Outdoor Use. This Sconce-Like Emergency Light Is Compact, Architecturally Designed and Suitable For Cold and Wet Weather Exposure.
Weight per unit	3.7 (lbs/each)
Product Category	Lighting

### Features

Hardware	No
Lamp Included	Yes
Lamp Type	LED - Static
lumens	225 LM
Material	Aluminum
Maximum Operating Temperature	50
media	Yes
Shape	Semi-Cylinder
Voltage Rating	120-277
Warranty	5
Wattage	3

### Material, Color, and Finish

Color	White
color temperature	4000
Finish	Textured
Lens Color	Clear
Lens Material	Acrylic

### Descriptions

Construction	New Construction
Description	LED EGRESS EMGCV WHITE
extra long description	LITH AFB OEL DWHGXD UVOLT N WT Basi
Long Description	The Affinity® AFB LED emergency light by Lithonia Lighting® is stylish and equally durable for indoor and outdoor use. This sconce-like emergency light is compact, architecturally designed and suitable for cold and wet weather exposure.
Product Type	Emergency Lighting Unit



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Lithonia Lighting
GTIN	00193047953139
Manufacturers Part Number	AFB OEL DWHGXD UVOLT N WT
UPC	193047953139

## Taxonomies, Classifications, and Categories

Category Description	Emergency & Exit Lighting
----------------------	---------------------------

## Packaging

Carton	1
Weight Per each	3.7

## Uses, Certifications, and Standards

Application	Education,Government,Healthcare,Hospitality,House of Worship,Offices & Banks,Retail
environmental conditions	OUTDOOR
Mounting	SURFACE
standard	C-UL-US,NFPA 101,NFPA 70,NOM,ULCA Title 20,ROHS