ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
8420 Tejas Loop
Laredo, TX 78045-0000
Phone: 9564620607
Fax: 9562846601



AHCL2130C CCL CONN 30A 120/208V 3PH 4P5W BL&BK

EATON WIRING DEVICES

Catalog Number	AHCL2130C
Manufacturer	EATON WIRING DEVICES
Description	Eaton Arrow Hart Color Coded Locking Connector, #14-8 AWG, 30A, Industrial, 3ØY 120/208 V, Back, Blue, Black, Ultra grip, Nylon, L21-30, Four-pole, Five-wire, Nylon, 0.38 - 1.16" (9.5 - 29.5mm)
Weight per unit	10.0 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

Dimensions	2.1300 IN X 2.3000 IN X 3.9400 IN
Media	Yes

Descriptions

Description	CCL CONN 30A 120/208V 3PH 4P5W BL&BK
Features	Eaton’s Arrow Hart color coded locking devices are an industry-first solution that adds six voltage rating color codes consistent with IEC 60309 standards to locking plugs, connectors, inlets, outlets and receptacles to provide you a quick, clear and easy way to identify your circuit voltage. Available in standard NEMA configurations for 20A and 30A applications, the devices ensure long-lasting, dependable service in the most demanding environments, are built with a contemporary flare and ergonomic design
Long Description	Eaton Arrow Hart Color Coded Locking Connector, #14-8 AWG, 30A, Industrial, 3ØY 120/208 V, Back, Blue, Black, Ultra grip, Nylon, L21-30, Four-pole, Five-wire, Nylon, 0.38 - 1.16" (9.5 - 29.5mm)
Product Type	CCL Conn 30A 120/208V 3PH 4P5W-BL&BK
Special Features	Industrial grd plugs & conns
Extra Long Description	EWD AHCL2130C CCL Conn 30A 120/208V

Manufacturer Information

Brand	Eaton
	Eaton Wiring Devices
GTIN	00032664755644
Manufacturers Part Number	AHCL2130C
UPC	781430

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Color Coded Locking

8420 Tejas Loop
Laredo, TX 78045-0000
Phone: 9564620607
Fax: 9562846601

Packaging

Carton	1
Package	40
Weight Per Each	10.0 (lbs/each)

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility - Other
Standard	cULus Listed,NOM,RoHS Compliant,NAFTA

Specifications







Eaton AHCL2130C

Eaton Arrow Hart Color Coded Locking Connector, #14-8 AWG, 30A, Industrial, 3ØY 120/208 V, Back, Blue, Black, Ultra grip, Nylon, L21-30, Four-pole, Five-wire, Nylon, 0.38 - 1.16" (9.5 - 29.5mm)

General specifications	
PRODUCT NAME	Eaton Arrow Hart Color Coded Locking Connector
CATALOG NUMBER	AHCL2130C
UPC	032664755644
PRODUCT LENGTH/DEPTH	2.13 in
PRODUCT HEIGHT	3.94 in
PRODUCT WIDTH	2.3 in
PRODUCT WEIGHT	0.001 lb
COMPLIANCES	RoHS Compliant NAFTA
CERTIFICATIONS	cULus Listed NOM
PRODUCT TYPE	Color Coded Locking

Product specifications

SPECIAL FEATURES	Voltage Color Coding
TYPE	Locking Connector
AMPERAGE RATING	30A
VOLTAGE RATING	3ØY 120/208 V
APPLICATION	Industrial
WIRING METHOD	Back
NUMBER OF WIRES	5
NUMBER OF POLES	Four-pole
COLOR	Black Blue
CORD DIAMETER	0.38-1.16 in (9.5-29.5 mm)
MATERIAL	Nylon
OPERATING TEMPERATURE	-40 to 60 °C (-40 to 140 °F)
ALLOWABLE WIRE SIZE	#14-8 AWG
NEMA CONFIGURATION	L21-30
TORQUE RATING	20 lbf-inch
DESIGN TYPE	Ultra grip
FACE/BODY MATERIAL	Nylon

Resources

MULTIMEDIA	Eaton Arrow Hart color coded locking devices
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - AHCL2130C Arrow Hart color coded industrial grade L21-30 locking devices spec sheet

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

© 2026 Eaton. All Rights Reserved.