



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AGW20 20A 32V 1/4X7/8 Fa Glass Fuse

*Bussmann Fuses*

Catalog Number	AGW20
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series Fast-Acting Fuse, Agw Series, 20A, 37 Vac, 32 VDC (Self Certified)
Weight per unit	0.0100 (lbs/each)
Product Category	Tools & Testers

### Features

amperage rating	20 Amp
connection	Ferrule End X Ferrule End
dimensions	0.8750 IN X 0.2500 IN X 0.2500 IN
Material	Glass tubeNickel-plated brass end cap construction
Voltage Rating	32 VAC

### Dimensions and Weight

Size	1/4 In Diameter X 7/8 In Length
------	---------------------------------

### Descriptions

Description	20A 32V 1/4X7/8 FA GLASS FUSE
extra long description	BUSS AGW-20 AGW GLASS FUSE - 1/4" x
Features	Eaton's Bussmann Division develops and manufactures critical circuit protection, power management and electrical safety products designed to provide innovative circuit and power electronics protection, serving the commercial, data center, electrical vehicle, food and beverage, and other markets.
Long Description	Eaton Bussmann series fast-acting fuse, AGW Series, 20A, 37 Vac, 32 Vdc (self certified)
Product Type	Agw Glass Fuse - 1/4" X 7/8" - 20 Amp
Special Features	Interrupt Rating 1000 Amp at 32 Vac, Material Glass Tube, Nickel Plated Brass Endcap

### Manufacturer Information

Brand	Eaton
GTIN	00051712704496
Manufacturers Part Number	AGW-20
UPC	051712704496

### Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Fast-Acting Fuse



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	5
Weight Per each	0.01

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	Not Applicable