



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AH430R5W 30A, 3PH 600V 3P4W Pin+Sleeve Receptacle

*Eaton Wiring Devices*

Catalog Number	AH430R5W
Manufacturer	Eaton Wiring Devices
Description	Receptacle Pin and Sleeve 30 Amp 3 Phase 600 Volt 3 Pole 4 Wire
Weight per unit	32.0 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	30
connection	Pin & Sleeve
dimensions	3.7500 IN X 4.2100 IN X 3.1250 IN
insulation	Nylon PA6-GF30FR (17)
Material	Nylon;Other
media	Yes
Phase	3
Poles	3
Voltage Rating	3Ø 600V/AC

### Material, Color, and Finish

Color	Blue & Gray
-------	-------------

### Dimensions and Weight

Size	5.5 x 4.75 x 5
------	----------------

### Descriptions

Description	30A,3PH 600V 3P4W PIN+SLEEVE RECEPTACLE
extra long description	CRS-H AH430R5W 30A 3PH 600V 3P4W PI
Features	Eaton's Arrow Hart full line of pin and sleeve devices offer sturdy nylon construction, rugged design with corrosion resistant components for lasting electrical performance, and watertight sealing that provides IP69K protection so you can feel confident in even the most severe washdown environments.
Long Description	RECEPTACLE PIN AND SLEEVE 30 AMP 3 PHASE 600 VOLT 3 POLE 4 WIRE
Product Type	30A 3PH 600V 3P4W Pin and Sleeve Recepta
Special Features	Watertight P&S receptacles

### Manufacturer Information

Brand	Eaton
GTIN	00326647319696
Manufacturers Part Number	AH430R5W
UPC	032664731969



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	RECEPTACLE

## Packaging

Carton	1
Package	32
Weight Per each	32

## Uses, Certifications, and Standards

Application	IEC 309 Products
environmental conditions	IP67 & IP69k
Mounting	Flange Mount
standard	IEC, UL, CSA
Temperature Rating	Max. 30°C (86°F) after 50 cycles of overload @150% of rated current