



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AYLV600PHWH Ariadni 450W Magnetic Low Voltage SP White Clam *Lutron*

Catalog Number	AYLV600PHWH
Manufacturer	Lutron
Description	Ariadni Dimmer, Magnetic Low-Voltage, Single-Pole, Preset, 120V/600VA (450W) Clamshell Packaging In White
Weight per unit	0.2500 (lbs/each)
Product Category	Lighting Dimmers

### Features

actuator	Toggle Switch
connection	Screw Terminal
Connection Type	Screw Terminal
insulation	Plastic
Material	Plastic/Metal
media	Yes
Poles	1
Switch Type	Toggle
Voltage Rating	120
Wattage	450

### Material, Color, and Finish

Color	White
Finish	Gloss

### Dimensions and Weight

Size	4.60 x 2.86;117 x 73
------	----------------------

### Descriptions

Description	ARIADNI 450W MAGNETIC LOW VOLTAGE SP WHITE CLAM
extra long description	LUT AYLV-600PH-WH ARIADNI LOW VOLT
Long Description	Ariadni Dimmer, Magnetic Low-Voltage, Single-pole, preset, 120V/600VA (450W) clamshell packaging in white
Product Type	Ariadni Low Volt 600VA Preset WH Clam
Special Features	Controls 600 VA (450 W) magnetic low-voltage loads. Toggle turn lights on/off. Slide up to brighten, down to dim.

### Manufacturer Information

Brand	Lutron
GTIN	00027557510219
Manufacturers Part Number	AYLV600PHWH
UPC	027557510219



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Preset dimmer, single-pole, clamshell packaging

## Packaging

Carton	6
Package	1
Weight Per each	0.25

## Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	Indoor use only
Frequency Rating	50 to 60
Mounting	WALLBOX
Operating Temperature	32 to 104
standard	UL, cUL