



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AYP0750 750 Al/Cu Offset Comp Terminal

Burndy LLC

Catalog Number	AYP0750
Manufacturer	Burndy LLC
Description	Aluminum Compression Pin Adapter, 700/750 Kcmil, 0.81" Plug Dia, 1.76" Plug Length, Al/Cu Rated.
Weight per unit	0.4800 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Conductor Type	CODE/FLEX
Die Index	936
insulation	Y
Insulation Type	Rubber
Material	Aluminum
pallet quantity	1776
Voltage Rating	35

Material, Color, and Finish

Color Code	YELLOW
Finish	Tin-Plated

Descriptions

Description	750 AL/CU OFFSET COMP TERMINAL
extra long description	BUR AYP0750 700/750KCMIL AL OFFSET
Long Description	Aluminum Compression Pin Adapter, 700/750 kcmil, 0.81" Plug Dia, 1.76" Plug Length, Al/Cu Rated.
Product Type	Terminal
Special Features	Features: All-Aluminum Electro-Tin Plated design eliminates possible bi-metallic corrosion and provides shortest connector length design possible for easy installation in equipment with limited space. Solid electro-tin plated aluminum plug makes properly connection easily. Smooth surface on the solic EC plug provides greater area contact establishing excellent conductivity. Solid plug has equivalent cross-sectional area as current carrying equivalent copper wire permitting use of larger aluminum wire to co

Manufacturer Information

Brand	BURNDY
GTIN	00781810738535
Manufacturers Part Number	AYPO750
UPC	781810738535



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Aluminum Pin Adapters

Packaging

Carton	1
Package	6
Weight Per each	0.48

Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B
Temperature Rating	194