



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ASZH240C300 3 Pole 240 V (240 V McOv) W/Out Mounting Bracket *Cooper Power Systems LLC*

Catalog Number	ASZH240C300
Manufacturer	Cooper Power Systems LLC
Description	Eaton Cooper Power Series Secondary Arrester, Storm Trapper He, McOv: 240 Vac, Voltage Rating: 240 Vac, 60 HZ, External Mount, Three-Pole, Without Mounting Bracket, Line Lead
Weight per unit	0.8000 (lbs/each)
Product Category	Tools & Testers

### Features

dimensions	4.2000 IN X 1.3000 IN X 2.2000 IN
Voltage Rating	240 VAC

### Descriptions

Description	3 POLE 240 V (240 V MCOV) W/OUT MOUNTING BRACKET
extra long description	ETN-LIPE ASZH240C300 240V STORM TRA
Features	Eaton's Cooper Power series low-voltage distribution-class surge arresters are designed to provide surge protection at distribution transformer secondary bushings, low voltage equipment and distribution circuits and have successfully passed all design tests for light duty distribution class arresters per IEEE Std C62.11 standard. Type L, Type S4 and Protective Gaps are used for addressing indoor and outdoor industrial applications from 175-650VAC.
Long Description	Eaton Cooper Power series secondary arrester, Storm Trapper HE, MCOV: 240 Vac, Voltage rating: 240 Vac, 60 Hz, External mount, Three-pole, Without mounting bracket, Line lead
Product Type	240V Storm Trap He 3

### Manufacturer Information

Brand	Eaton
GTIN	00194006066709
Manufacturers Part Number	ASZH240C300
UPC	194006066709

### Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Secondary arrester

### Packaging

Carton	1
Package	10
Weight Per each	0.8



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application .....	Utility .....
Frequency Rating .....	60 Hz .....
Mounting .....	External .....
standard .....	Not Applicable, Sans objet, IEEE C62-11, IEEE C62-11 .....