



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BRDC230240 BRDC Breaker 1-30/2P 1-40/2P Com. Trip 120/240V 10 *Eaton Corp*

Catalog Number	BRDC230240
Manufacturer	Eaton Corp
Description	Eaton BR Thermal Magnetic Circuit Breaker, Type BR 1-Inch Quad Circuit Breaker, (2) 30 A, (2) 40 A, 10 Kaic, Four-Pole, 120/240V, BRD, Common Breaker Trip, #14-4 Awg Cu/Al, BRD, Type BR Loadcenters
Weight per unit	0.8000 (lbs/each)
Product Category	Quadplex Standard Trip Plug-In

### Features

dimensions	3.0000 IN X 2.0000 IN X 3.0000 IN
interrupt rating	10 kAIC
Poles	4
Trip Type	Common breaker trip
Voltage Rating	120/240 V

### Descriptions

Description	BRDC BREAKER 1-30/2P 1-40/2P COM. TRIP 120/240V 10
extra long description	ETN BRDC230240 BRDC 1-30/2P 1-40/2P
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch quad circuit breaker, (2) 30 A, (2) 40 A, 10 kAIC, Four-pole, 120/240V, BRD, Common breaker trip, #14-4 AWG Cu/Al, BRD, Type BR Loadcenters
Product Type	BRDC 1-30/2P 1-40/2P 120/240V 10K

### Manufacturer Information

Brand	Eaton
GTIN	00786676372336
Manufacturers Part Number	BRDC230240
UPC	786676372336

### Taxonomies, Classifications, and Categories

Category Description	Specialty Breakers (Quad, Dupl, Shunt Trip)
Type	Thermal magnetic circuit breakers



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.8

## Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative Energy Marine Vessels and Equipment - Marine Vessels and Equipment - Other
standard	Generation - Conventional Energy - Conventional Energy Datacenters - IT Space: CI and Hyper Converged UL 489, Federal Specifications Classification W-C375