



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BISR10 1/0AWG In-Line Splice

Burndy LLC

Catalog Number	BISR10
Manufacturer	Burndy LLC
Description	Aluminum In-Line Splice, 14-1/0 Awg.
Weight per unit	0.1300 (lbs/each)
Product Category	Small Terminals & Connectors

Features

Conductor Size	14-1/0 AWG
Insulation Type	Plastisol
Material	Aluminum
Operating Voltage	600 V

Descriptions

Description	1/0AWG IN-LINE SPLICE
extra long description	BUR BISR1/0 1/0-14 IN-LINE SPLICE
Long Description	Aluminum In-Line Splice, 14-1/0 AWG.
Product Type	SPLICE REDUCER
Special Features	Features: Clear Plastisol Covered AL6061-T6 Aluminum Body: Saves Time, Lowers Installation Costs, Eliminates Taping, Clear Plastisol: Allows Visual Confirmation That Conductor Is Properly Inserted, Oxide Inhibitor Pre-Installed: Inhibits Moisture And Contaminants From Entering The Contact Area, Range-Taking: Reduces Number Of Connectors Carried In Inventory, UL486B Listed, Dual-Rated AL9CU For Any Stranded Copper Or Stranded Aluminum Applications, 600 Volt, 90 DEG C, Wire Entry: In-Line, Torque: 50 IN-LB,

Manufacturer Information

Brand	BURNDY
GTIN	00781810134115
Manufacturers Part Number	BISR1/0
UPC	781810134115

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	BISR

Packaging

Carton	1
Package	100
Weight Per each	0.13



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	For Indoor Use Only, Copper Or Stranded Aluminum
standard	UL 486A-486B
Temperature Rating	194