



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BR230ST Type BR BRKR 30A/2 Pole 120/240V 10K W/Shunt Trip

*Eaton Corp*

Catalog Number	BR230ST
Manufacturer	Eaton Corp
Description	Eaton BR Thermal Magnetic Circuit Breaker, Type BR Breakers, 30 A, 10 Kaic, Two-Pole, 120/240V, BR, Common Breaker Trip, #14-4 Awg Cu/Al, Q28, BR, Type BR Loadcenters, Shunt Trip Included
Weight per unit	1.0 (lbs/each)
Product Category	2 Pole Standard Trip Plug-In

### Features

dimensions	4.5000 IN X 4.2500 IN X 4.0000 IN
interrupt rating	10 kAIC
Poles	2
Trip Type	Common breaker trip
Voltage Rating	120/240 V

### Descriptions

Description	TYPE BR BRKR 30A/2 POLE 120/240V 10K W/SHUNT TRIP
extra long description	ETN BR230ST BR 30A/2 Pole 120/240V
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR thermal magnetic circuit breaker, Type BR breakers, 30 A, 10 kAIC, Two-pole, 120/240V, BR, Common breaker trip, #14-4 AWG Cu/Al, Q28, BR, Type BR Loadcenters, Shunt trip included
Product Type	BR 30A/2 Pole 120/240V 10K W/Shunt Trip
Special Features	120Vac Shunt trip

### Manufacturer Information

Brand	Eaton
GTIN	00786676000239
Manufacturers Part Number	BR230ST
UPC	786676000239

### Taxonomies, Classifications, and Categories

Category Description	Specialty Breakers (Quad, Dupl, Shunt Trip)
Type	Thermal magnetic circuit breakers

### Packaging

Carton	1
Weight Per each	1



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Marine Vessels and Equipment - Marine Vessels and Equipment -  
OtherOtherGeneration - Renewable Energy - Alternative  
EnergyGeneration - Conventional Energy - Conventional  
EnergyDatacenters - IT Space: CI and Hyper Converged

standard

UL 489, Federal Specifications Classification W-C375