

Eaton BRHH2125

Catalog Number: BRHH2125

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 125 A, 42 kAIC, Two-pole, 120/240V, BRH, Common breaker trip, #4-2/0 AWG Cu/Al, Q28, BRH, Type BR Loadcenters

General specifications



Product Name

Eaton BR thermal magnetic circuit breaker

Catalog Number

BRHH2125

UPC

786676377003

Product Length/Depth

3 in

Product Height

3 in

Product Width

2 in

Product Weight

0.55 lb

Compliances

Federal Specifications Classification W-C376

Certifications

UL 490

Catalog Notes

10-150A. single-, two- and three-pole, selected amperage available in switching duty, HACR, shunt trip and high magnetic setting

defaultTaxonomyAttributeLabel

Type

Type BR 1-Inch plug-on circuit breaker

Amperage Rating

125 A

Voltage rating

120/240 V

Trip Type

Common breaker trip

Circuit breaker type

BR

Used with

Type BR Loadcenters

Mounting Method

Plug-on

Interrupt rating

42 kAIC

Main circuit breaker

BRH

Wire size

#4-2/0 AWG Cu/Al

Number of poles

Two-pole

Quantity

28

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRHH2125](#)

[Metering Equipment - Utilities Servicing Texas](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

Eaton BRHH2125

Catalog Number: BRHH2125

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 125 A, 42 kAIC, Two-pole, 120/240V, BRH, Common breaker trip, #4-2/0 AWG Cu/Al, Q28, BRH, Type BR Loadcenters

General specifications



Product Name

Eaton BR thermal magnetic circuit breaker

Catalog Number

BRHH2125

UPC

786676377003

Product Length/Depth

3 in

Product Height

3 in

Product Width

2 in

Product Weight

0.55 lb

Compliances

Federal Specifications Classification W-C376

Certifications

UL 490

Catalog Notes

10-150A. single-, two- and three-pole, selected amperage available in switching duty, HACR, shunt trip and high magnetic setting



Powering Business Worldwide

defaultTaxonomyAttributeLabel

Type

Type BR 1-Inch plug-on circuit breaker

Amperage Rating

125 A

Voltage rating

120/240 V

Trip Type

Common breaker trip

Circuit breaker type

BR

Used with

Type BR Loadcenters

Mounting Method

Plug-on

Interrupt rating

42 kAIC

Main circuit breaker

BRH

Wire size

#4-2/0 AWG Cu/Al

Number of poles

Two-pole

Quantity

28

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRHH2125](#)

[Metering Equipment - Utilities Servicing Texas](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)