



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C0075E2AFB 75 Va Type Mte Control Transformer With Primary Fu

Eaton Corp

Catalog Number	C0075E2AFB
Manufacturer	Eaton Corp
Description	Eaton Type Mte Industrial Control Transformer, PV: 240 X 480V, 230 X 460V, 220 X 440V, Taps: None, SV: 120/115/110V, Cu Magnet Wire, 55°C, 75 Va
Weight per unit	3.5 (lbs/each)
Product Category	Encapsulated Industrial Contro

Features

dimensions	3.8600 IN X 3.0000 IN X 4.0400 IN
kva rating	75 VA
Primary Voltage	240 x 480 V230 x 460 V220 x 440 V
Secondary Voltage	120/115/110 V
Tap Size	NONE

Descriptions

Description	75 VA TYPE MTE CONTROL TRANSFORMER WITH PRIMARY FU
extra long description	ETN C0075E2AFB 75VA Type MTE CPT W/
Features	Eaton offers a complete line of Type AP, MTE and MTK Industrial Control Transformers, which provide stepped-down voltages to machine tool control devices. Each unit must pass rigid tests for turns ratio, insulation, continuity, and over potential. Performance meets or exceeds ANSI/NEMA ST-1 requirements. With a 50-60 Hz operation standard, transformers are designed for loads requiring extremely good regulation. Regulation also exceeds ANSI/NEMA requirements.
Long Description	Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, taps: none, sv: 120/115/110v, cu magnet wire, 55°C, 75 va
Product Type	75VA Type Mte CPT W/ Prim Fuse Block
Special Features	Primary Fuse Block

Manufacturer Information

Brand	Eaton
GTIN	00786680420825
Manufacturers Part Number	C0075E2AFB
UPC	786680420825

Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Industrial Control Transformer



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	3.5

Uses, Certifications, and Standards

Application	Other
standard	cUL Certified,UL Listed,CSA Certified,RoHS Compliant
Temperature Rating	55°C