ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BT2MC0 7.9" 18LB BLK Nylon CBL Tie

Panduit Corporation

Catalog Number	BT2MC0
Manufacturer	Panduit Corporation
Description	The Dome-Top® BT2M-C0 Cable Tie Provides Dependable Bundling For Indoor/Outdoor Routing and Organization Requiring Uv and Weather Resistance. Miniature Cross Section, 7.9 In (201MM) Long With 18 LB (80 N) Minimum Loop Tensile Strength and A 0.06–2 In (1.5–50.8MM) Bundle Diameter Range. It Is Black Nylon 6.6 (Uv-Resistant, Weather-Resistant). Operating Range -76 to 185°F (-60 to 85°C). Use With GTS-E, GS2B-E, PTS, PPTS, and STS2 Tools.
Weight per unit	0.1770 (lbs/each)
Product Category	Cable Ties & Wraps

Features

media	Yes
Tensile Strength	18

Dimensions and Weight

Length	7.9
Thickness	0.05

Descriptions

Description	7.9" 18LB BLK NYLON CBL TIE
extra long description	PAN BT2M-C0 Cable Tie, Black UV PA6
Long Description	The Dome-Top® BT2M-C0 cable tie provides dependable bundling for indoor/outdoor routing and organization requiring UV and weather resistance. Miniature cross section, 7.9 in (201mm) long with 18 lb (80 N) minimum loop tensile strength and a 0.06–2 in (1.5–50.8mm) bundle diameter range. It is black Nylon 6.6 (UV-Resistant, Weather-Resistant). Operating range -76 to 185°F (-60 to 85°C). Use with GTS-E, GS2B-E, PTS, PPTS, and STS2 tools.
Product Type	Cable Tie, Black Uv PA6.6, 7.9"L (201MM), 18LB, PK100
Special Features	Indoor/Outdoor

Manufacturer Information

Brand	Panduit®
GTIN	00074983602865
Manufacturers Part Number	BT2M-C0
UPC	074983602865

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie

Availability

minimum qty	100

Packaging

Carton	100
Package	1000
Weight Per each	0.177

Uses, Certifications, and Standards

standard	UL 62275 (File E56854), CSA-C22.2 No. 62275, 11130200, NRC 10CFR50, QPL-AS23190, CSA Certified, RoHS Compliant