



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C0350E2AFB 350 Va Type Mte Control Transformer With Primary F

Eaton Corp

Catalog Number	C0350E2AFB
Manufacturer	Eaton Corp
Description	Eaton Type Mte Industrial Control Transformer, PV: 240 X 480V, 230 X 460V, 220 X 440V, Taps: None, SV: 120/115/110V, 55°C, 350 Va
Weight per unit	14.0 (lbs/each)
Product Category	Encapsulated Industrial Contro

Features

dimensions	4.5600 IN X 4.5000 IN X 5.2900 IN
kva rating	350 VA
Primary Voltage	220 X 440 V, 230 X 460 V, 240 X 480 V
Secondary Voltage	120/115/110 V
Tap Size	NONE

Descriptions

Description	350 VA TYPE MTE CONTROL TRANSFORMER WITH PRIMARY F
extra long description	ETN C0350E2AFB 350VA Type MTE CPT W
Features	Eaton offers a complete line of Type AP, MTE and MTK Industrial Control Transformers, which provide stepped-down voltages to machine tool control devices. Each unit must pass rigid tests for turns ratio, insulation, continuity, and over potential. Performance meets or exceeds ANSI/NEMA ST-1 requirements. With a 50-60 Hz operation standard, transformers are designed for loads requiring extremely good regulation. Regulation also exceeds ANSI/NEMA requirements.
Long Description	Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, taps: none, sv: 120/115/110v, 55°c, 350 va
Product Type	350VA Type Mte CPT W/ Prim Fuse Block
Special Features	Primary Fuse Block

Manufacturer Information

Brand	Eaton
GTIN	00786680420948
Manufacturers Part Number	C0350E2AFB
UPC	786680420948

Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Industrial Control Transformer



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	14

Uses, Certifications, and Standards

Application	Other
standard	UL Listed,CSA Certified,cUL Certified,RoHS Compliant
Temperature Rating	55°C