

Eaton C0500E6U

Catalog Number: C0500E6U

Eaton Type MTE industrial control transformer, pv:
240/416/480/600v, 230/400/460/575v, 220/380/440/550v,
208/500v, cu magnet wire, taps: none, sv: 99/120/130v,
95/115/125v, 91/110/120v, 85/100/110v, 55°C, 500 va

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Type MTE industrial control transformer	C0500E6U
	UPC
	786680019159

Product Length/Depth	Product Height
7.008 in	4.449 in

Product Width	Product Weight
5.236 in	25.6 lb

Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	CSA Certified
	cUL Certified
	UL Listed

Catalog Notes

Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Physical Attributes

Coil material

Copper windings

Design

MTE

Tap size

None

Performance Ratings

Primary voltage

208/500 V, 220/380/440/550 V, 230/400/460/575 V,
240/416/480/600 V

Temperature rating

55°C

Volt ampere rating

500 VA

Secondary voltage

99/120/130 V, 95/115/125 V, 91/110/120 V, 85/100/110 V

Resources

Specifications and datasheets

[Eaton Specification Sheet - C0500E6U](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton C0500E6U

Catalog Number: C0500E6U

Eaton Type MTE industrial control transformer, pv:
240/416/480/600v, 230/400/460/575v, 220/380/440/550v,
208/500v, cu magnet wire, taps: none, sv: 99/120/130v,
95/115/125v, 91/110/120v, 85/100/110v, 55°C, 500 va

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Type MTE industrial control transformer	C0500E6U
	UPC
	786680019159

Product Length/Depth	Product Height
7.008 in	4.449 in

Product Width	Product Weight
5.236 in	25.6 lb

Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	CSA Certified
	cUL Certified
	UL Listed

Catalog Notes

Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Physical Attributes

Coil material

Copper windings

Design

MTE

Tap size

None

Performance Ratings

Primary voltage

208/500 V, 220/380/440/550 V, 230/400/460/575 V,
240/416/480/600 V

Temperature rating

55°C

Volt ampere rating

500 VA

Secondary voltage

99/120/130 V, 95/115/125 V, 91/110/120 V, 85/100/110 V

Resources

Specifications and datasheets

[Eaton Specification Sheet - C0500E6U](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)