

# Specifications

Photo is representative



## Eaton C0050E3A

Eaton Type MTE industrial control transformer, pv: 208/277v, taps: none, sv: 120v, 55°C, 50 va

### General specifications

PRODUCT NAME	Eaton Type MTE industrial control transformer
CATALOG NUMBER	C0050E3A
UPC	786680550003
PRODUCT LENGTH/DEPTH	3.61 in
PRODUCT HEIGHT	3.26 in
PRODUCT WIDTH	3 in
PRODUCT WEIGHT	2.8 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL Listed CSA Certified cUL Certified
CATALOG NOTES	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

### Physical Attributes

COIL MATERIAL	Copper windings
DESIGN	MTE
TAP SIZE	None

### Performance Ratings

PRIMARY VOLTAGE	208/277 V
TEMPERATURE RATING	55°C
VOLT AMPERE RATING	50 VA
SECONDARY VOLTAGE	120 V

### Resources

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - C0050E3A](#)

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights  
Reserved.

Eaton is a registered trademark.

All other trademarks are property of  
their respective owners.

Follow us on social media to get the latest  
product and support information.

