

# Specifications

Photo is representative

## Eaton CCP15034CD RS

Eaton Crouse-Hinds series PowerMate CCP plug, 150A, 0.875-1.906", Three-wire, four-pole, Style 2, Copper-free aluminum, Reverse service, 600 Vac/250 Vdc

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series PowerMate CCP plug
<b>CATALOG NUMBER</b>	CCP15034CD RS
<b>UPC</b>	662276277465
<b>PRODUCT LENGTH/DEPTH</b>	10.8 in
<b>PRODUCT HEIGHT</b>	4.13 in
<b>PRODUCT WIDTH</b>	4.13 in
<b>PRODUCT WEIGHT</b>	2.2 lb



### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEMA RATING</b>	4X

### Product specifications

<b>AMPERAGE RATING</b>	150A
<b>GROUNDING TYPE</b>	Style 2
<b>CONFIGURATION</b>	Three-wire, four-pole
<b>CABLE DIAMETER</b>	0.875-1.906"
<b>VOLTAGE RATING</b>	600 Vac/250 Vdc
<b>MATERIAL</b>	Copper-free aluminum
<b>SPECIAL FEATURES</b>	Reverse service

### Resources

<b>BROCHURES</b>	<a href="#">PowerMate Drilling Pin and Sleeve Devices brochure</a>
------------------	--

<b>CATALOGS</b>	<a href="#">PowerMate Drilling Pin and Sleeve Devices catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">PowerMate Drilling Pin and Sleeve Devices cUL certification (Plugs and Connectors)</a>
	<a href="#">PowerMate Drilling Pin and Sleeve Devices UL certification (Plugs and Connectors)</a>
<b>INSTALLATION INSTRUCTIONS</b>	<a href="#">IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices</a>
	<a href="#">IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">PowerMate Connectors</a>
	<a href="#">Eaton Specification Sheet - CCP15034CD RS</a>

---

**PROJECT NAME:**

---

**PROJECT NUMBER:**

---

**PREPARED BY:**

---

**DATE:**



**Eaton Corporation plc**  
 Eaton House  
 30 Pembroke Road  
 Dublin 4, Ireland  
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



# Specifications

Photo is representative

## Eaton CCP15034CD RS

Eaton Crouse-Hinds series PowerMate CCP plug, 150A, 0.875-1.906", Three-wire, four-pole, Style 2, Copper-free aluminum, Reverse service, 600 Vac/250 Vdc

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series PowerMate CCP plug
<b>CATALOG NUMBER</b>	CCP15034CD RS
<b>UPC</b>	662276277465
<b>PRODUCT LENGTH/DEPTH</b>	10.8 in
<b>PRODUCT HEIGHT</b>	4.13 in
<b>PRODUCT WIDTH</b>	4.13 in
<b>PRODUCT WEIGHT</b>	2.2 lb



### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEMA RATING</b>	4X

### Product specifications

<b>AMPERAGE RATING</b>	150A
<b>GROUNDING TYPE</b>	Style 2
<b>CONFIGURATION</b>	Three-wire, four-pole
<b>CABLE DIAMETER</b>	0.875-1.906"
<b>VOLTAGE RATING</b>	600 Vac/250 Vdc
<b>MATERIAL</b>	Copper-free aluminum
<b>SPECIAL FEATURES</b>	Reverse service

### Resources

<b>BROCHURES</b>	<a href="#">PowerMate Drilling Pin and Sleeve Devices brochure</a>
------------------	--

<b>CATALOGS</b>	<a href="#">PowerMate Drilling Pin and Sleeve Devices catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">PowerMate Drilling Pin and Sleeve Devices cUL certification (Plugs and Connectors)</a>
	<a href="#">PowerMate Drilling Pin and Sleeve Devices UL certification (Plugs and Connectors)</a>
<b>INSTALLATION INSTRUCTIONS</b>	<a href="#">IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices</a>
	<a href="#">IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">PowerMate Connectors</a>
	<a href="#">Eaton Specification Sheet - CCP15034CD RS</a>

---

**PROJECT NAME:**

---

**PROJECT NUMBER:**

---

**PREPARED BY:**

---

**DATE:**

---



**Eaton Corporation plc**  
 Eaton House  
 30 Pembroke Road  
 Dublin 4, Ireland  
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

