

# Specifications



Photo is representative



## Eaton C0075E2AFB

Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, taps: none, sv: 120/115/110v, cu magnet wire, 55°C, 75 va

### Physical Attributes

<b>COIL MATERIAL</b>	Copper windings
<b>DESIGN</b>	MTE
<b>TAP SIZE</b>	None

### General specifications

<b>PRODUCT NAME</b>	Eaton Type MTE industrial control transformer
<b>CATALOG NUMBER</b>	C0075E2AFB
<b>UPC</b>	786680420825
<b>PRODUCT LENGTH/DEPTH</b>	3.86 in
<b>PRODUCT HEIGHT</b>	4.04 in
<b>PRODUCT WIDTH</b>	3 in
<b>PRODUCT WEIGHT</b>	3.4 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	UL Listed CSA Certified cUL Certified
<b>CATALOG NOTES</b>	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation

# Specifications



Photo is representative



## Eaton C0075E2AFB

Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, taps: none, sv: 120/115/110v, cu magnet wire, 55°C, 75 va

### Physical Attributes

<b>COIL MATERIAL</b>	Copper windings
<b>DESIGN</b>	MTE
<b>TAP SIZE</b>	None

### General specifications

<b>PRODUCT NAME</b>	Eaton Type MTE industrial control transformer
<b>CATALOG NUMBER</b>	C0075E2AFB
<b>UPC</b>	786680420825
<b>PRODUCT LENGTH/DEPTH</b>	3.86 in
<b>PRODUCT HEIGHT</b>	4.04 in
<b>PRODUCT WIDTH</b>	3 in
<b>PRODUCT WEIGHT</b>	3.4 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	UL Listed CSA Certified cUL Certified
<b>CATALOG NOTES</b>	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation