

Eaton C0150E5EFB

Catalog Number: C0150E5EFB

Eaton Type MTE industrial control transformer, pv: 200/220/440v, 208/230/460v, 240/480v, sv: 23/110v, 24/115v, 25/120v, 55°c, 150 va , cu magnet wire

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Type MTE industrial control transformer	C0150E5EFB
	UPC
	786680421761
Product Length/Depth	Product Height
3.96 in	4.65 in
Product Width	Product Weight
3.75 in	8.5 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL Listed
	cUL Certified
	CSA Certified

Catalog Notes

Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Physical Attributes

Coil material

Copper windings

Design

MTE

Tap size

None

Performance Ratings

Primary voltage

200/220/440 V, 208/230/460 V, 240/480 V

Temperature rating

55°C

Volt ampere rating

150 VA

Secondary voltage

23/110 V, 24/115 V, 25/120 V

Miscellaneous

Modification 1

Factory-mounted two-pole primary fuse block for non-rejection type fuses

Special features

Primary fuse block

Resources

Specifications and datasheets

[Eaton Specification Sheet - C0150E5EFB](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton C0150E5EFB

Catalog Number: C0150E5EFB

Eaton Type MTE industrial control transformer, pv: 200/220/440v, 208/230/460v, 240/480v, sv: 23/110v, 24/115v, 25/120v, 55°C, 150 va , cu magnet wire

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Type MTE industrial control transformer	C0150E5EFB
	UPC
	786680421761
Product Length/Depth	Product Height
3.96 in	4.65 in
Product Width	Product Weight
3.75 in	8.5 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL Listed
	cUL Certified
	CSA Certified

Catalog Notes

Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Physical Attributes

Coil material

Copper windings

Design

MTE

Tap size

None

Performance Ratings

Primary voltage

200/220/440 V, 208/230/460 V, 240/480 V

Temperature rating

55°C

Volt ampere rating

150 VA

Secondary voltage

23/110 V, 24/115 V, 25/120 V

Miscellaneous

Modification 1

Factory-mounted two-pole primary fuse block for non-rejection type fuses

Special features

Primary fuse block

Resources

Specifications and datasheets

[Eaton Specification Sheet - C0150E5EFB](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)