

# Specifications



Photo is representative



## Eaton C0150E5EFB

Eaton Type MTE industrial control transformer, pv: 200/220/440v, 208/230/460v, 240/480v, sv: 23/110v, 24/115v, 25/120v, 55°c, 150 va , cu magnet wire

### General specifications

<b>PRODUCT NAME</b>	Eaton Type MTE industrial control transformer
<b>CATALOG NUMBER</b>	C0150E5EFB
<b>UPC</b>	786680421761
<b>PRODUCT LENGTH/DEPTH</b>	3.96 in
<b>PRODUCT HEIGHT</b>	4.65 in
<b>PRODUCT WIDTH</b>	3.75 in
<b>PRODUCT WEIGHT</b>	8.5 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	UL Listed cUL Certified CSA Certified
<b>CATALOG NOTES</b>	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability



Powering Business Worldwide

## Physical Attributes

COIL MATERIAL	Copper windings
DESIGN	MTE
TAP SIZE	None

## Performance Ratings

PRIMARY VOLTAGE	200/220/440 V, 208/230/460 V, 240/480 V
TEMPERATURE RATING	55°C
VOLT AMPERE RATING	150 VA
SECONDARY VOLTAGE	23/110 V, 24/115 V, 25/120 V

## Miscellaneous

MODIFICATION 1	Factory-mounted two-pole primary fuse block for non-rejection type fuses
SPECIAL FEATURES	Primary fuse block

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - C0150E5EFB</a>
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



Photo is representative



## Eaton C0150E5EFB

Eaton Type MTE industrial control transformer, pv: 200/220/440v, 208/230/460v, 240/480v, sv: 23/110v, 24/115v, 25/120v, 55°c, 150 va , cu magnet wire

### General specifications

<b>PRODUCT NAME</b>	Eaton Type MTE industrial control transformer
<b>CATALOG NUMBER</b>	C0150E5EFB
<b>UPC</b>	786680421761
<b>PRODUCT LENGTH/DEPTH</b>	3.96 in
<b>PRODUCT HEIGHT</b>	4.65 in
<b>PRODUCT WIDTH</b>	3.75 in
<b>PRODUCT WEIGHT</b>	8.5 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	UL Listed cUL Certified CSA Certified
<b>CATALOG NOTES</b>	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability



Powering Business Worldwide

## Physical Attributes

COIL MATERIAL	Copper windings
DESIGN	MTE
TAP SIZE	None

## Performance Ratings

PRIMARY VOLTAGE	200/220/440 V, 208/230/460 V, 240/480 V
TEMPERATURE RATING	55°C
VOLT AMPERE RATING	150 VA
SECONDARY VOLTAGE	23/110 V, 24/115 V, 25/120 V

## Miscellaneous

MODIFICATION 1	Factory-mounted two-pole primary fuse block for non-rejection type fuses
SPECIAL FEATURES	Primary fuse block

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - C0150E5EFB</a>
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

