



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C0200E2A 200 Va Type Mte Control Transformer

Eaton Corp

Catalog Number	C0200E2A
Manufacturer	Eaton Corp
Description	Eaton Type Mte Industrial Control Transformer, PV: 240 X 480V, 230 X 460V, 220 X 440V, SV: 120/115/110V, 55°C, 200 Va , Cu Magnet Wire
Weight per unit	8.0 (lbs/each)
Product Category	Encapsulated Industrial Contro

Features

dimensions	4.1800 IN X 4.5000 IN X 4.2200 IN
kva rating	200 VA
Primary Voltage	220 X 440 V, 230 X 460 V, 240 X 480 V
Secondary Voltage	120/115/110 V
Tap Size	NONE

Descriptions

Description	200 VA TYPE MTE CONTROL TRANSFORMER
extra long description	ETN C0200E2A Control transformer, 2
Features	Eaton offers a complete line of Type AP, MTE and MTK Industrial Control Transformers, which provide stepped-down voltages to machine tool control devices. Each unit must pass rigid tests for turns ratio, insulation, continuity, and over potential. Performance meets or exceeds ANSI/NEMA ST-1 requirements. With a 50-60 Hz operation standard, transformers are designed for loads requiring extremely good regulation. Regulation also exceeds ANSI/NEMA requirements.
Long Description	Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, sv: 120/115/110v, 55°c, 200 va , cu magnet wire
Product Type	Control Transformer, 200VA, 240/480-120
Special Features	Primary Fuse Block

Manufacturer Information

Brand	Eaton
GTIN	00786680422607
Manufacturers Part Number	C0200E2A
UPC	786680422607



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description CONTROL TRANSFORMERS

Type Industrial Control Transformer

Packaging

Carton 1

Weight Per each 8

Uses, Certifications, and Standards

Application Other

standard CSA Certified,UL Listed,cUL Certified,RoHS Compliant

Temperature Rating 55°C