

Specifications



Eaton CH20L125C

Eaton CH 3/4-inch loadcenter, single-phase, 20 circuits, 20-pole, #6-2/0 wire, 125Amp, NEMA 1

General specifications

PRODUCT NAME	Eaton CH main lug loadcenter
CATALOG NUMBER	CH20L125C
UPC	782113097572
PRODUCT LENGTH/DEPTH	29.13 in
PRODUCT HEIGHT	3.88 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	15 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL 50 UL 67

CATALOG NOTES

Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard.

Product specifications

TYPE	Main lug only
AMPERAGE RATING	125 A
BUS MATERIAL	Copper
COVER	Ch8cf-combination, ch8cs-surface
FEED TYPE	Top/bottom
MAIN CIRCUIT BREAKER	CH
NUMBER OF CIRCUITS	20
NUMBER OF SPACES	20
PHASE	Single-phase
WIRE SIZE	#6-2/0 AWG
BOX SIZE	C
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3



Powering Business Worldwide

Specifications



Eaton CH20L125C

Eaton CH 3/4-inch loadcenter, single-phase, 20 circuits, 20-pole, #6-2/0 wire, 125Amp, NEMA 1

General specifications

PRODUCT NAME	Eaton CH main lug loadcenter
CATALOG NUMBER	CH20L125C
UPC	782113097572
PRODUCT LENGTH/DEPTH	29.13 in
PRODUCT HEIGHT	3.88 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	15 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL 50 UL 67

CATALOG NOTES

Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard.

Product specifications

TYPE	Main lug only
AMPERAGE RATING	125 A
BUS MATERIAL	Copper
COVER	Ch8cf-combination, ch8cs-surface
FEED TYPE	Top/bottom
MAIN CIRCUIT BREAKER	CH
NUMBER OF CIRCUITS	20
NUMBER OF SPACES	20
PHASE	Single-phase
WIRE SIZE	#6-2/0 AWG
BOX SIZE	C
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3



Powering Business Worldwide