

Specifications



Eaton CH20L125C

Eaton CH 3/4-inch loadcenter, single-phase, 20 circuits, 20-pole, #6-2/0 wire, 125Amp, NEMA 1

General specifications

| | |
|-----------------------------|------------------------------|
| PRODUCT NAME | Eaton CH main lug loadcenter |
| CATALOG NUMBER | CH20L125C |
| UPC | 782113097572 |
| PRODUCT LENGTH/DEPTH | 29.13 in |
| PRODUCT HEIGHT | 3.88 in |
| PRODUCT WIDTH | 14.31 in |
| PRODUCT WEIGHT | 15 lb |
| WARRANTY | Limited lifetime |
| CERTIFICATIONS | UL 50 UL 67 |

CATALOG NOTES

Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard.

Product specifications

| | |
|-----------------------------|----------------------------------|
| TYPE | Main lug only |
| AMPERAGE RATING | 125 A |
| BUS MATERIAL | Copper |
| COVER | Ch8cf-combination, ch8cs-surface |
| FEED TYPE | Top/bottom |
| MAIN CIRCUIT BREAKER | CH |
| NUMBER OF CIRCUITS | 20 |
| NUMBER OF SPACES | 20 |
| PHASE | Single-phase |
| WIRE SIZE | #6-2/0 AWG |
| BOX SIZE | C |
| ENCLOSURE | NEMA 1 |
| ENCLOSURE MATERIAL | Metallic |
| INTERRUPT RATING | 25 kAIC |
| NUMBER OF WIRES | 3 |



Powering Business Worldwide