

Specifications



Photo is representative



Eaton C0250E6U

Eaton Type MTE industrial control transformer, pv: 240/416/480/600v, 230/400/460/575v, 220/380/440/550v, 208/500v, taps: none, sv: 99/120/130v, 95/115/125v, 91/110/120v, 85/100/110v, 55°C, 250 va

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Type MTE industrial control transformer |
| CATALOG NUMBER | C0250E6U |
| UPC | 786680019135 |
| PRODUCT LENGTH/DEPTH | 5.866 in |
| PRODUCT HEIGHT | 3.819 in |
| PRODUCT WIDTH | 4.488 in |
| PRODUCT WEIGHT | 14.7 lb |
| WARRANTY | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| COMPLIANCES | RoHS Compliant |
| CERTIFICATIONS | cUL Certified UL Listed CSA Certified |
| CATALOG NOTES | Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability |



Powering Business Worldwide

Physical Attributes

| | |
|----------------------|-----------------|
| COIL MATERIAL | Copper windings |
| DESIGN | MTE |
| TAP SIZE | None |

Performance Ratings

| | |
|---------------------------|--|
| PRIMARY VOLTAGE | 208/500 V, 220/380/440/550 V, 230/400/460/575 V, 240/416/480/600 V |
| TEMPERATURE RATING | 55°C |
| VOLT AMPERE RATING | 250 VA |
| SECONDARY VOLTAGE | 99/120/130 V, 95/115/125 V, 91/110/120 V, 85/100/110 V |

Resources

| | |
|--------------------------------------|--|
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - C0250E6U |
|--------------------------------------|--|

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.



Specifications



Photo is representative



Eaton C0250E6U

Eaton Type MTE industrial control transformer, pv: 240/416/480/600v, 230/400/460/575v, 220/380/440/550v, 208/500v, taps: none, sv: 99/120/130v, 95/115/125v, 91/110/120v, 85/100/110v, 55°C, 250 va

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Type MTE industrial control transformer |
| CATALOG NUMBER | C0250E6U |
| UPC | 786680019135 |
| PRODUCT LENGTH/DEPTH | 5.866 in |
| PRODUCT HEIGHT | 3.819 in |
| PRODUCT WIDTH | 4.488 in |
| PRODUCT WEIGHT | 14.7 lb |
| WARRANTY | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| COMPLIANCES | RoHS Compliant |
| CERTIFICATIONS | cUL Certified UL Listed CSA Certified |
| CATALOG NOTES | Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability |



Powering Business Worldwide

Physical Attributes

| | |
|----------------------|-----------------|
| COIL MATERIAL | Copper windings |
| DESIGN | MTE |
| TAP SIZE | None |

Performance Ratings

| | |
|---------------------------|--|
| PRIMARY VOLTAGE | 208/500 V, 220/380/440/550 V, 230/400/460/575 V, 240/416/480/600 V |
| TEMPERATURE RATING | 55°C |
| VOLT AMPERE RATING | 250 VA |
| SECONDARY VOLTAGE | 99/120/130 V, 95/115/125 V, 91/110/120 V, 85/100/110 V |

Resources

| | |
|--------------------------------------|--|
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - C0250E6U |
|--------------------------------------|--|

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.

