



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CH250GF 2P 50A Ground Fault Breaker

Eaton Corp

Catalog Number	CH250GF
Manufacturer	Eaton Corp
Description	Eaton CH Gfci Circuit Breaker, Ground Fault Circuit Breaker, 50 A, 10 Kaic, Two-Pole, 120/240 V, CH, Common, Plug-On, #14-6 Awg Cu/Al, Type CH Loadcenters, Ground Fault Circuit Interrupter, GFI
Weight per unit	0.9800 (lbs/each)
Product Category	In Circuit Breakers

Features

amperage rating	50 A
connection	Plug-on
interrupt rating	10 kAIC
Poles	Two-pole
Trip Type	Common
Voltage Rating	120/240 V

Dimensions and Weight

Height	2 in
Length	6 in
Width	2 in

Descriptions

Description	2P 50A GROUND FAULT BREAKER
extra long description	ETN CH250GF
Features	Eaton's residential CH circuit breakers provide premium overload protection. The Type CH circuit breakers trip to the OFF position, eliminating nuisance callbacks. The CHF family also includes a trip flag to differentiate between a trip and the breaker being turned off. The thermal-magnetic trip curve avoids nuisance tripping on mild overloads while reacting almost instantaneously to severe short-circuit conditions. Multiple breakers have an internal common trip connection to operate all poles simultaneous
Long Description	Eaton CH GFCI circuit breaker,Ground fault circuit breaker,50 A,10 kAIC,Two-pole,120/240 V,CH,Common,Plug-on,#14-6 AWG Cu/Al,Type CH Loadcenters,Ground fault circuit interrupter,GFI
Product Type	CH250GF

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113912899
Manufacturers Part Number	CH250GF
UPC	782113912899



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Fault Sensing Breakers (AFCI/GFCI)
Type	GFCI circuit breakers

Packaging

Carton	1
Weight Per each	0.98

Uses, Certifications, and Standards

standard	UL 489
----------	--------