



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## C371E2 Operator Mechanism

Eaton Corp

Catalog Number	C371E2
Manufacturer	Eaton Corp
Description	Type C371 Circuit Breaker Operator Mechanism, 150A Frame, Flange Mounted, 6.5-16 Variable Depth Mounting Range, HMCP and Series C-Ehd, FDB, FD, FDC, HFD, Ed-Frame, For Nema 4-4X Enclosures, With 4-Inch Handle
Weight per unit	6.0 (lbs/each)
Product Category	Circuit Breaker Accessories

### Features

amperage rating	150A
dimensions	16.6000 IN X 6.7000 IN X 5.1000 IN
media	Yes

### Descriptions

Description	OPERATOR MECHANISM
extra long description	ETN C371E2 OPERATOR MECHANISM
Features	Eaton's Electrical Sector under the Eaton brand offers the widest variety of molded case circuit breakers available today. Designed for electrical and machinery OEMs serving a range of industries and applications these proven designs incorporate the latest in innovation with the high reliability that has been our hallmark since the advent of the circuit breaker in the 1920s
Long Description	Type C371 Circuit Breaker Operator Mechanism, 150A frame, Flange mounted, 6.5-16 variable depth mounting range, HMCP and Series C-EHD, FDB, FD, FDC, HFD, ED-frame, For NEMA 4-4X enclosures, With 4-inch handle
Product Type	Operator Mechanism

### Manufacturer Information

Brand	Eaton
GTIN	00782113599540
Manufacturers Part Number	C371E2
UPC	782113599540

### Taxonomies, Classifications, and Categories

Category Description	Powerdefense Breakers
Type	Molded case circuit breaker accessory

### Packaging

Carton	1
Weight Per each	6



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Power Distribution and Control
Mounting	FLANGE
standard	UL Listed,IEC Rated,IEC/EN 60947-4-1